PSR-SCF- 24UC/URM/4X1/2X2 - Coupling relay

2981444

https://www.phoenixcontact.com/us/products/2981444

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safe coupling relay with force-guided contacts, 4 N/O contacts, 2 N/C contacts, fixed screw terminal block, width: 40 mm

Your advantages

- Suitable up to category 1, PL c (EN ISO 13849-1), SIL 1 (EN IEC 62061), SIL 1 (IEC 61508)
- Safe readback due to force-guided signal contact in accordance with EN 50205
- Easy proof test according to IEC 61508 thanks to integrated signal contact
- 1 or 2-channel control
- 4 enabling current paths, 2 confirmation current paths

Commercial data

Item number	2981444
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN01
Product key	DNA162
GTIN	4017918987787
Weight per piece (including packing)	130 g
Weight per piece (excluding packing)	103 g
Customs tariff number	85364900
Country of origin	DE

Technical data

Product properties

Product type	Coupling relay
Product family	PSRclassic
Application	Safe switch off
	High demand
	Low demand
Control	1 and 2 channel
Mechanical service life	10x 10^6 cycles
Relay type	Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Times

Typ. starting time with U_s	typ. 10 ms (with U_s when controlled via A1)
Typical release time	typ. 10 ms (with U_s when controlled via A1)
Restart time	< 1 s (Boot time)
Recovery time	< 500 ms

Electrical properties

Maximum power dissipation for nominal condition	8.71 W (at U_B = 26.4 V DC, U_S = 24 V, I_S = 52 mA, n = 1, I_L^2 = 72 A², $R_{contact}$ = 0.1 Ω)
Nominal operating mode	100% operating factor
Rated insulation voltage	250 V
Rated surge voltage/insulation	Safe isolation, reinforced insulation 6 kV between input circuit (A1/A2) and all output current paths
	Basic insulation 4 kV between all output current paths

Supply

Designation	A1/A2
Rated control circuit supply voltage U_S	24 V AC/DC -20 % ... +10 %
Rated control supply current I_S	typ. 52 mA
Power consumption at U_S	typ. 1.25 W
Filter time	1 ms (at A1-A2; test pulse width)
	1 s (at A1-A2; test pulse rate)

Output data

Relay: Enabling current paths (13/14, 23/24, 33/34, 43/44)

Number of outputs	4
Contact switching type	4 enabling current paths
Contact material	$AgSnO_2$

Switching voltage	min. 5 V AC/DC
	max. 250 V AC/DC
Switching power	min. 50 mW
Inrush current	min. 10 mA
	max. 6 A
Switching capacity	5 A (AC15, 250 V)
	5 A (DC13, 24 V)
Limiting continuous current	6 A
Sq. Total current	72 A^2
Switching frequency	max. 0.5 Hz
Mechanical service life	10x 10^6 cycles
Interrupting rating (ohmic load) max.	see load limit curve
Maximum interrupting rating (inductive load)	48 W (N/O contact, 24 V DC, τ = 40 ms)
	40 W (N/O contact, 48 V DC, τ = 40 ms)
	36 W (N/O contact, 60 V DC, τ = 40 ms)
	35 W (N/O contact, 110 V DC, τ = 40 ms)
	33 W (N/O contact, 220 V DC, τ = 40 ms)
Output fuse	10 A gL/gG NEOZED
	4 A gL/gG NEOZED (Low demand)

Relay: Confirmation current paths (51/52, 61/62)

Number of outputs	2
Contact switching type	2 confirmation current paths
Contact material	$AgSnO_2$
Switching voltage	min. 5 V AC/DC
	max. 250 V AC/DC
Switching power	min. 50 mW
Inrush current	min. 10 mA
	max. 6 A
Switching capacity	5 A (DC13, 24 V)
	5 A (AC15, 250 V)
Limiting continuous current	6 A
Sq. Total current	72 A^2
Mechanical service life	10x 10^6 cycles
Output fuse	6 A gL/gG NEOZED

Connection data

Connection technology

pluggable	no

Conductor connection

Connection method	Screw connection
Conductor cross-section rigid	0.2 mm² ... 2.5 mm²
Conductor cross-section flexible	0.2 mm² ... 2.5 mm²

Conductor cross-section AWG	24 ... 12
Stripping length	7 mm
Screw thread	M3
Tightening torque	0.6 Nm

Signaling

Operating voltage display	1 x LED (green)

Dimensions

Width	40 mm
Height	111 mm
Depth	55 mm

Material specifications

Color (Housing)	green (RAL 6021)
Housing material	PBT

Characteristics

Safety data

Stop category (EN 60204-1)	0

Safety data: EN ISO 13849

Performance level (PL)	c

Safety data: IEC 61508 - High demand

Safety Integrity Level (SIL)	1

Safety data: IEC 61508 - Low demand

Safety Integrity Level (SIL)	1

Safety data

Safety Integrity Level (SIL)	1

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Maximum altitude	≤ 2000 m (Above sea level)
Max. permissible humidity (storage/transport)	75 % (on average, 85% infrequently, non-condensing)
Max. permissible relative humidity (operation)	75 % (on average, 85% infrequently, non-condensing)
Shock	15g (In the event of stress caused by shock, contact reactions are possible for up to 2 ms.)
Vibration (operation)	10 Hz ... 150 Hz, 2g (In the event of stress caused by vibration, contact reactions are possible for up to 2 ms.)

Approvals

CE


Certificate	CE-compliant

Mounting

Mounting type	DIN rail mounting
Mounting position	vertical or horizontal

Drawings

Block diagram



Block diagram

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2981444

Functional Safety
Approval ID: 3535 2399

Functional Safety
Approval ID: 3535 2399

cULus Listed
Approval ID: E140324

cULus Listed
Approval ID: E140324

Functional Safety
Approval ID: 4478015124312

Functional Safety
Approval ID: 4478015124312

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

ETIM

ETIM 10.0	EC001437

UNSPSC

UNSPSC 21.0	39122300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	d0a72710-ff17-48a1-b7e4-f7e242e59526

EF3.1 Climate Change

CO2e kg	2.133 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com