

PSBJ-URTK/SS GY - Test plug strip



3029017

<https://www.phoenixcontact.com/us/products/3029017>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug strip, color: gray

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3029017 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BE19 |
| Product key | BE1Z3X |
| GTIN | 4017918161897 |
| Weight per piece (including packing) | 1.56 g |
| Weight per piece (excluding packing) | 1.544 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

PSBJ-URTK/SS GY - Test plug strip



3029017

<https://www.phoenixcontact.com/us/products/3029017>

Technical data

Product properties

| | |
|--------------|-------------|
| Product type | Test socket |
|--------------|-------------|

Dimensions

| | |
|--------|------|
| Width | 6 mm |
| Height | 6 mm |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 27,5 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

PSBJ-URTK/SS GY - Test plug strip



3029017

<https://www.phoenixcontact.com/us/products/3029017>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250304 |
| ECLASS-15.0 | 27250304 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002555 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 20122000 |
|-------------|----------|

PSBJ-URTK/SS GY - Test plug strip



3029017

<https://www.phoenixcontact.com/us/products/3029017>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com