

PLC-BSC-TTL/1 - Relay base

2982689

<https://www.phoenixcontact.com/us/products/2982689>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



6.2 mm PLC basic terminal block for TTL signal with screw connection, without relay or solid-state relay, for mounting on DIN rail NS 35/7,5, 1 N/O contact, input voltage TTL (5 V DC)

Your advantages

- 6.2 mm narrow design width
- Screw and spring-cage connection
- RT III protection
- Safe isolation in accordance with EN 50178 (VDE 0160)
- 4 kV_{rms} electrical isolation between coil and contact
- Status indicator
- Bridging options

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2982689 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | C461 |
| Product key | DK6221 |
| GTIN | 4046356155212 |
| Weight per piece (including packing) | 30.94 g |
| Weight per piece (excluding packing) | 30 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

Technical data

Notes

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Product properties

| | |
|----------------|-----------------------|
| Product type | Relay socket |
| Product family | PLC-INTERFACE |
| Application | TTL signal at input |
| Operating mode | 100% operating factor |

Input data

| | |
|-----------------------------|--|
| Nominal input voltage U_N | 5 V DC (TTL) |
| | The nominal voltage of the plug-on electromechanical relay or solid-state relay (see necessary accessories) deviates from the nominal input voltage of the base with integrated upstream circuit |
| | 5 V DC (TTL) |
| | The nominal voltage of the plug-on electromechanical relay or solid-state relay (see necessary accessories) deviates from the nominal input voltage of the base with integrated upstream circuit |

Relay assembly

| | |
|--|-----------------------------|
| Rated control circuit supply voltage U_S | 5 V DC |
| Voltage range with reference to U_S | 0.9 ... 1.2 |
| Rated control supply current I_S | 41 mA |
| Rated actuating voltage U_C | 5 V DC (TTL) |
| Voltage range with reference to U_C | 0.9 ... 1.2 |
| Rated actuating current I_C | 2.5 mA |
| Typical response time | 4.5 ms |
| Typical release time | 3.5 ms |
| Operating voltage display | Yellow LED |
| Protective circuit | Reverse polarity protection |
| | Surge protection |
| Surge voltage protection | > 6.5 V |

Optocoupler assembly

| | |
|---|--------------|
| Rated control circuit supply voltage U_S | 5 V DC |
| Voltage range with reference to U_S | 0.9 ... 1.2 |
| Rated control supply current I_S | 11.5 mA |
| Rated actuating voltage U_C | 5 V DC (TTL) |
| Rated actuating current I_C | 2.5 mA |
| Switching level 1 signal ("H") (TTL signal) | > 2 V DC |
| Switching level 0 signal ("L") (TTL signal) | < 0.8 V DC |

PLC-BSC-TTL/1 - Relay base



2982689

<https://www.phoenixcontact.com/us/products/2982689>

| | |
|---------------------------|-----------------------------|
| Typical response time | 35 μ s |
| Typical release time | 320 μ s |
| Operating voltage display | Yellow LED |
| Protective circuit | Reverse polarity protection |
| | Surge protection |
| Transmission frequency | 1000 Hz |
| Surge voltage protection | > 6.5 V |

Output data

| | |
|--|-----------------------------|
| Maximum switching voltage | 48 V DC |
| Minimum switching voltage | 3 V DC |
| Limiting continuous current | 100 mA |
| Voltage drop at max. limiting continuous current | < 1 V |
| Output circuit | 2-conductor, floating |
| Protective circuit | Reverse polarity protection |
| | Surge protection |
| Maximum switching voltage | 33 V DC |
| Minimum switching voltage | 3 V DC |
| Limiting continuous current | 3 A |
| Voltage drop at max. limiting continuous current | < 200 mV |
| Maximum inrush current | 15 A (10 ms) |
| Output circuit | 2-conductor, floating |
| Protective circuit | Reverse polarity protection |
| | Surge protection |

Connection data

| | |
|----------------------------------|--|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 2.5 mm ² |
| | 0.2 mm ² ... 2.5 mm ² (Single ferrule) |
| | 2x 0.5 mm ² ... 1.5 mm ² (TWIN ferrule) |
| Conductor cross-section AWG | 26 ... 14 |
| Tightening torque | 0.45 Nm ... 0.55 Nm (Usually these terminal blocks must be supported during conductor connection (held by one hand, supported on the housing)) |

Dimensions

| | |
|-----------------|--------|
| Item dimensions | |
| Width | 6.2 mm |
| Height | 80 mm |
| Depth | 94 mm |

Material specifications

PLC-BSC-TTL/1 - Relay base



2982689

<https://www.phoenixcontact.com/us/products/2982689>

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

Approvals

Corrosive gas test

| | |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
| | EN 60068-2-60 |

Standards and regulations


| | |
|-----------------------|----------------|
| Standards/regulations | IEC/EN 60664-1 |
|-----------------------|----------------|

Mounting

| | |
|-------------------|---------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | in rows with zero spacing |
| Mounting position | any |

Drawings

Diagram




① AC, ohmic load

② DC, ohmic load

Max. interrupting rating

Circuit diagram




PLC-BSC-TTL/1 - Relay base

2982689

<https://www.phoenixcontact.com/us/products/2982689>



Circuit diagram



PLC-BSC-TTL/1 - Relay base



2982689

<https://www.phoenixcontact.com/us/products/2982689>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2982689>



cUL Recognized
Approval ID: E238705



UL Recognized
Approval ID: E238705



EAC
Approval ID: RU D-DE.B*00573/18



UL Listed
Approval ID: FILE E 172140



cUL Listed
Approval ID: FILE E 172140

PLC-BSC-TTL/1 - Relay base

2982689

<https://www.phoenixcontact.com/us/products/2982689>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371603 |
| ECLASS-15.0 | 27371603 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001456 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

2982689

<https://www.phoenixcontact.com/us/products/2982689>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 9389f072-1be7-4b04-963d-0e3b01028b42 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com