

IB IL 24 SDI 8-PAC - Safety module



2985657

<https://www.phoenixcontact.com/us/products/2985657>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safe, decentral, digital input module, IP20 degree of protection for the Inline product range. This module has four safe digital inputs with two-channel occupancy or eight safe digital inputs with single-channel occupancy.

Product description

The safety module is an input module from the Inline product range and can be used in an INTERBUS-Safety system. The safety module can be used as a part of an Inline station at any point within an INTERBUS-Inline system. The transmission speed of the safety module can be set to 500 kBaud or 2 Mbaud using a switch. Only one transmission speed must be used uniformly within an INTERBUS system. The module has four safe digital inputs with two-channel occupancy or eight safe digital inputs with single-channel occupancy.

The parameters of the inputs can be set in accordance with the application and make it possible to integrate sensors in the safe INTERBUS (INTERBUS-Safety).

In an INTERBUS Safety system, you can achieve the following safety integrity by using the safety module depending on the installation and parameterization:

- Up to category 4 according to the EN 954-1 standard
- Up to SIL 3 according to the standards EN 61508 and EN 62061
- Up to PL e according to the prEN ISO 13849-1 standard

The input data is exchanged between the safe INTERBUS controller and the module using safe messages (see UM DE INTERBUS-SAFETY SYS).

Your advantages

- SIL 3 according to IEC/EN 61508
- SIL 3 in accordance with EN IEC 62061
- PL e in accordance with EN ISO 13849-1

Commercial data

Item number	2985657
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DN03
Product key	DNA421
GTIN	4046356131629
Weight per piece (including packing)	243.1 g
Weight per piece (excluding packing)	216.11 g
Customs tariff number	85389091
Country of origin	DE

IB IL 24 SDI 8-PAC - Safety module



2985657

<https://www.phoenixcontact.com/us/products/2985657>

Technical data

Dimensions

Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Material specifications

Color	yellow
-------	--------

Interfaces

Inline local bus

Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (can be switched)

System properties

Programming data

ID code (dec.)	175
Process data channel	see safety data

Input data

Digital:

Input name	Digital inputs
Number of inputs	4 (for 2-channel assignment) 8 (for 1-channel assignment)
Connection method	Spring-cage connection
Connection technology	2-, 3-, 4-conductor
Input voltage	24 V DC (parameterizable; see technical data.)
Input voltage range "0" signal	-3 V DC ... 5 V DC
Input voltage range "1" signal	11 V DC ... 30 V DC
Typical response time	See technical data

Product properties

Product type	I/O component
Product family	Inline
Application	IB-Safety

IB IL 24 SDI 8-PAC - Safety module



2985657

<https://www.phoenixcontact.com/us/products/2985657>

Type	modular
Diagnostics messages	Short-circuit or overload of the digital outputs Error message in diagnostics code (bus) and display by means of the LED on the motor

Electrical properties

Maximum power dissipation for nominal condition	150 W
Transmission medium	Copper

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (see safety data)
Current draw	max. 230 mA (see safety data)

Potentials: Main circuit supply (U_M)

Supply voltage	24 V DC (see safety data)
----------------	---------------------------

Potentials: Segment circuit supply (U_S)

Supply voltage	24 V (see safety data)
----------------	------------------------

Supply: Module electronics

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC

Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 50 Hz, 1 min

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Inline connector

Connection method	Spring-cage connection
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 hPa ... 108 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	66 hPa ... 108 kPa (up to 3000 m above sea level)

IB IL 24 SDI 8-PAC - Safety module



2985657

<https://www.phoenixcontact.com/us/products/2985657>

Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Permissible humidity (storage/transport)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL 24 SDI 8-PAC - Safety module

2985657

<https://www.phoenixcontact.com/us/products/2985657>



Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com