
WST 1,5 - Warning cover

3030958

https://www.phoenixcontact.com/us/products/3030958

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Warning cover, Strip, yellow (RAL 1018), labeled, mounting type: plug in, for terminal block width: 4.25 mm, Number of individual labels: 5

Your advantages

- Accidental actuation of the terminal points is prevented
- Warning labels and warning covers serve to cover and identify mains terminal blocks
- The warning labels snap into the screw and actuation shafts of the relevant terminal block
- Can be isolated lengthwise and crosswise

Commercial data

Item number	3030958
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG20
Product key	BG2511
GTIN	4017918193096
Weight per piece (including packing)	0.297 g
Weight per piece (excluding packing)	0.29 g
Customs tariff number	49119900
Country of origin	PL

Technical data

Product properties

Product type	Terminal marker
Number of positions	5
Pitch	4.25 mm

Marking

Number of individual labels	5
Number of individual labels per row	5
Identification technology	Plotter

Dimensions

Width	3.55 mm
Height	4.25 mm
Depth	4.50 mm
Pitch	4.25 mm

Material specifications

Color	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08

Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type	plug in

Classifications

ECLASS

ECLASS-15.0	27281107
ECLASS-13.0	27281107

ETIM

ETIM 10.0	EC001777

UNSPSC

UNSPSC 21.0	55121700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.008 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com