


# MT 1,5-QUATTRO-PE - Protective conductor terminal block



3001695

<https://www.phoenixcontact.com/us/products/3001695>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective conductor terminal block, When aligning with a feed-through terminal block of the same shape, an end cover must be interposed for insulation voltages of  $> 320\text{ V}$ , number of connections: 4, connection method: Screw connection, cross section:  $0.14\text{ mm}^2 - 1.5\text{ mm}^2$ , mounting type: NS 15, color: green-yellow

## Your advantages

- Corrosion-free terminal points
- Low contact resistance
- Captive terminal block screws
- Green-yellow housing

## Commercial data

Item number	3001695
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE12
Product key	BE1261
GTIN	4017918107208
Weight per piece (including packing)	4.89 g
Weight per piece (excluding packing)	4.89 g
Customs tariff number	85369010
Country of origin	TR

# MT 1,5-QUATTRO-PE - Protective conductor terminal block



3001695

<https://www.phoenixcontact.com/us/products/3001695>

## Technical data

### Notes

General	When aligning with a feed-through terminal block of the same shape, an end cover must be interposed for insulation voltages of > 320 V
---------	--

### Product properties

Product type	Ground terminal block
Number of connections	4
Number of rows	2

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	4 kV
Maximum power dissipation for nominal condition	0.56 W

### Connection data

Grounding foot	Yes
Number of connections per level	4
Nominal cross section	1.5 mm <sup>2</sup>
Connection method	Screw connection
Screw thread	M2
Note	Please observe the current carrying capacity of the DIN rails.
Tightening torque	0.22 ... 0.25 Nm
Stripping length	6 mm
Internal cylindrical gage	A1
Connection in acc. with standard	IEC 60947-7-2
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Cross section AWG	26 ... 16 (converted acc. to IEC)
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	26 ... 16 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>

### Dimensions

Width	4.2 mm
Height	33.5 mm
Depth on NS 15	30 mm

### Material specifications

Color	green-yellow
-------	--------------

# MT 1,5-QUATTRO-PE - Protective conductor terminal block



3001695

<https://www.phoenixcontact.com/us/products/3001695>

Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

## Mechanical properties

### Mechanical data

Open side panel	No
-----------------	----

## Environmental and real-life conditions

### Oscillation/broadband noise

Specification	EN 50155:2021-07
Spectrum	Long life test category 2, bogie-mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	$6.12 \text{ (m/s}^2\text{)}^2\text{/Hz}$
Acceleration	$30.6 \text{ m/s}^2$
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

### Shocks

Pulse shape	Half-sine
Acceleration	$300 \text{ m/s}^2$
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

# MT 1,5-QUATTRO-PE - Protective conductor terminal block



3001695

<https://www.phoenixcontact.com/us/products/3001695>

## Standards and regulations

Connection in acc. with standard

IEC 60947-7-2

## Mounting

Mounting type

NS 15

# MT 1,5-QUATTRO-PE - Protective conductor terminal block




3001695

<https://www.phoenixcontact.com/us/products/3001695>

## Drawings

Circuit diagram



# MT 1,5-QUATTRO-PE - Protective conductor terminal block




3001695


<https://www.phoenixcontact.com/us/products/3001695>

## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3001695>

 <b>CSA</b> Approval ID: 13631				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	-	-	28 - 14	-

 <b>EAC</b> Approval ID: KZ7500651131219505				
---	--	--	--	--

 <b>cULus Recognized</b> Approval ID: E60425				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
B	-	-	30 - 14	-
F	-	-	30 - 14	-
D	-	-	30 - 14	-

<b>CCA</b> Approval ID: NTR-NL 4242				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine	-	-	-	- 1.5

 <b>BV</b> Approval ID: 07774/E0 BV				
---	--	--	--	--

<b>DNV</b> Approval ID: TAE00001CT				
---------------------------------------	--	--	--	--

# MT 1,5-QUATTRO-PE - Protective conductor terminal block



3001695

<https://www.phoenixcontact.com/us/products/3001695>

## Classifications

### ECLASS

ECLASS-13.0	27250103
ECLASS-15.0	27250103

### ETIM

ETIM 10.0	EC000901
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# MT 1,5-QUATTRO-PE - Protective conductor terminal block



3001695

<https://www.phoenixcontact.com/us/products/3001695>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.015 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)