

UK 5-RETURN - Feed-through terminal block



3002597

<https://www.phoenixcontact.com/us/products/3002597>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Universal terminal block with screw connection, cross section: 0.2 mm² ... 4 mm², AWG: 30 - 10, width: 6.2 mm, color: gray

Commercial data

Item number	3002597
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE12
Product key	BE1211
GTIN	4017918090364
Weight per piece (including packing)	11.216 g
Weight per piece (excluding packing)	10.91 g
Customs tariff number	85369010
Country of origin	PL

UK 5-RETURN - Feed-through terminal block



3002597

<https://www.phoenixcontact.com/us/products/3002597>

Technical data

Product properties

Product type	Feed-through terminal block
Number of connections	2
Number of rows	2
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
---------------------	------

Connection data

Number of connections per level	2
---------------------------------	---

Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm
Stripping length	8 mm
Connection in acc. with standard	IEC / EN
Conductor cross-section rigid	0.2 mm ² ... 6 mm ²
Cross section AWG	24 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section, flexible [AWG]	24 ... 8 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 4 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 2.5 mm ²
Cross-section with insertion bridge, rigid	4 mm ²
Cross-section with insertion bridge, flexible	4 mm ²
2 conductors with same cross section, rigid	0.2 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible	0.2 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1.5 mm ²
Nominal current	41 A
Maximum load current	41 A (with 6 mm ² conductor cross-section)
Nominal voltage	500 V
Connection in acc. with standard	UL
Cross section AWG	30 ... 10 (converted acc. to IEC)
Nominal current	30 A
Nominal voltage	300 V

UK 5-RETURN - Feed-through terminal block



3002597

<https://www.phoenixcontact.com/us/products/3002597>

Connection in acc. with standard	CSA
Nominal current	40 A
Nominal voltage	300 V

Dimensions

Width	6.2 mm
-------	--------

Material specifications

Color	gray
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Electrical tests

Surge voltage test

Test voltage setpoint	7.3 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 4 mm ²	0.48 kA
Short-time withstand current 6 mm ²	0.72 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	1.89 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 32/NS 35
Test force setpoint	5 N
Result	Test passed

UK 5-RETURN - Feed-through terminal block



3002597

<https://www.phoenixcontact.com/us/products/3002597>

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	0.2 mm ² / 0.2 kg
	4 mm ² / 0.9 kg
	6 mm ² / 1.4 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Standards and regulations

Connection in acc. with standard	IEC / EN
	UL
	CSA

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32


UK 5-RETURN - Feed-through terminal block

3002597

<https://www.phoenixcontact.com/us/products/3002597>

Drawings

Circuit diagram



1 = cover

2 = fixed bridge, for cross-connections in the terminal center, screw heads with insulating collar

3 = fixed bridge, for cross-connections in the terminal center, with crimped-on rollers

4 = insertion bridge

5 = separating plate

6 = partition plate

UK 5-RETURN - Feed-through terminal block



3002597

<https://www.phoenixcontact.com/us/products/3002597>

Classifications

UNSPSC

UNSPSC 21.0	39121410
-------------	----------

UK 5-RETURN - Feed-through terminal block



3002597

<https://www.phoenixcontact.com/us/products/3002597>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com