

FBSR 1/7/13/16-8 - Plug-in bridge



3033821

<https://www.phoenixcontact.com/us/products/3033821>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in bridge, non-adjacent, pitch: 8.2 mm, number of positions: 16, nominal current: 32 A, pin assignment: 1, 7, 13, 16, color: red

Commercial data

Item number	3033821
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z2X
GTIN	4046356862042
Weight per piece (including packing)	14.54 g
Weight per piece (excluding packing)	9.99 g
Customs tariff number	85366990
Country of origin	CN

3033821

<https://www.phoenixcontact.com/us/products/3033821>

Technical data

Product properties

Product type	Plug-in bridge
Number of positions	16
Pitch	8.2 mm

Electrical properties

Maximum load current	32 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Connection data

Maximum load current	32 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Dimensions

Width	129.5 mm
Height	30 mm
Depth	30 mm
Pitch	8.2 mm

Material specifications

Color	red (RAL 3001)
Material	Copper
Flammability rating according to UL 94	V0
Insulating material	PA

Mechanical properties

Technical data

Pin assignment	1, 7, 13, 16
----------------	--------------

Mounting

Mounting type	Plug-in mounting
---------------	------------------

FBSR 1/7/13/16-8 - Plug-in bridge



3033821

<https://www.phoenixcontact.com/us/products/3033821>

Classifications

ECLASS

ECLASS-13.0

27250303

ETIM

ETIM 9.0

EC000489

UNSPSC

UNSPSC 21.0

39121400

FBSR 1/7/13/16-8 - Plug-in bridge



3033821

<https://www.phoenixcontact.com/us/products/3033821>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com