

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block



3002611

<https://www.phoenixcontact.com/us/products/3002611>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse modular terminal block, fuse type: Glass / ceramics / ..., fuse type: G / 5 x 20, nom. voltage: 500 V, nominal current: 28 A, connection method: Push-in connection, Rated cross section: 4 mm², cross section: 0.2 mm²- 6 mm², connection method: Push-in connection, Rated cross section: 4 mm², cross section: 0.2 mm²- 6 mm², mounting type: NS 35/7,5, NS 35/15, color: black

Your advantages

- Time-saving conductor connection thanks to tool-free direct-connection technology
- Convenient plugging with lower insertion force
- Easy integration and replacement of fuses with the lever element
- High conductor pull-out forces due to the spring design
- Full flexibility thanks to the standardized CLIPLINE complete bridging, marking, and testing accessories
- Easy checking of the fuses with optical signal unit

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3002611 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE22 |
| Product key | BE2236 |
| GTIN | 4055626370248 |
| Weight per piece (including packing) | 27.64 g |
| Weight per piece (excluding packing) | 27.64 g |
| Customs tariff number | 85369095 |
| Country of origin | IN |

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block



3002611

<https://www.phoenixcontact.com/us/products/3002611>

Technical data

Notes

| | |
|--------------------|---|
| Order information: | Fuse-link not supplied as standard |
| General | The current is determined by the fuse used, the voltage by the selected LED. If the fuse is faulty, the downstream circuit will not be disconnected. |

Product properties

| | |
|-----------------------|---------------------|
| Product type | Fuse terminal block |
| Number of connections | 4 |
| Number of rows | 3 |
| Potentials | 2 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--|
| Fuse type | Glass / ceramics / ... |
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 1.02 W |
| Fuse | G / 5 x 20 |
| LED voltage range | 30 V AC/DC ... 60 V AC/DC |
| LED current range | 0.4 mA ... 0.86 mA |
| Maximum power dissipation | max. 1.6 W (with single arrangement of the fuse terminal block in the event of overload) max. 1.6 W (With interconnected arrangement of several fuse terminal blocks in the event of overload) max. 4 W (with single arrangement of the fuse terminal block in the event of a short-circuit) max. 2.5 W (With interconnected arrangement of several fuse terminal blocks in the event of a short-circuit) |

Input data

| | |
|-------------------|---------------------------|
| LED voltage range | 30 V AC/DC ... 60 V AC/DC |
|-------------------|---------------------------|

Connection data

| | |
|---------------------------------|-------------------|
| Number of connections per level | 2 |
| Nominal cross section | 4 mm ² |

Level 1

| | |
|----------------------------------|--------------------|
| Connection method | Push-in connection |
| Stripping length | 10 mm ... 12 mm |
| Internal cylindrical gage | A4 |
| Connection in acc. with standard | IEC 60947-7-3 |

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block



3002611

<https://www.phoenixcontact.com/us/products/3002611>

| | |
|---|--|
| Conductor cross-section rigid | 0.2 mm ² ... 6 mm ² |
| Cross section AWG | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.2 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible ultrasound-compressed | 0.34 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] ultrasound-compressed | 22 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² ... 1 mm ² |
| Nominal cross section | 4 mm ² |
| Nominal current | 28 A |
| Maximum load current | 32 A (with 6 mm ² conductor cross-section, rigid) |
| Nominal voltage | 500 V |

Level 2

| | |
|---|--|
| Connection method | Push-in connection |
| Stripping length | 10 mm ... 12 mm |
| Connection in acc. with standard | IEC 60947-7-3 |
| Conductor cross-section rigid | 0.2 mm ² ... 6 mm ² |
| Cross section AWG | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.2 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Conductor cross-section flexible (2 conductors with the same cross-section, with TWIN ferrule and plastic sleeve) | 0.5 mm ² ... 1 mm ² |
| Nominal cross section | 4 mm ² |
| Nominal current | 6.3 A |
| Maximum load current | 6.3 A (the current is determined by the fuse used) |
| Nominal voltage | 60 V (the voltage is determined by the light indicator.) |

Level 1 Connection cross sections directly pluggable

| | |
|---|---|
| Conductor cross-section rigid | 0.5 mm ² ... 6 mm ² |
| Conductor cross-section, rigid [AWG] | 20 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.5 mm ² ... 4 mm ² |

Level 2 Connection cross sections directly pluggable

| | |
|---|---|
| Conductor cross-section rigid | 0.5 mm ² ... 6 mm ² |
| Conductor cross-section, rigid [AWG] | 20 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.5 mm ² ... 4 mm ² |

Ex data

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block



3002611

<https://www.phoenixcontact.com/us/products/3002611>

Rated data (ATEX/IECEX)

| | |
|--|-------------------------------------|
| Identification | ⊕ II 3 G Ex ec IIC Gc |
| Operating temperature range | -60 °C ... 130 °C |
| Ex-certified accessories | 3002619 D-PT 4-PE/L/HESI |
| | 1205066 SZS 1,0X4,0 VDE |
| | 3022276 CLIPFIX 35-5 |
| | 3022218 CLIPFIX 35 |
| List of bridges | Plug-in bridge / FBS 2-6 / 3030336 |
| | Plug-in bridge / FBS 3-6 / 3030242 |
| | Plug-in bridge / FBS 4-6 / 3030255 |
| | Plug-in bridge / FBS 5-6 / 3030349 |
| | Plug-in bridge / FBS 10-6 / 3030271 |
| | Plug-in bridge / FBS 20-6 / 3030365 |
| Bridge data | 19 A / 4 mm ² |
| for bridging with bridge | 275 V |
| - At bridging between non-adjacent terminal blocks | 275 V |
| - At cut-to-length bridging with cover | 275 V |
| Rated insulation voltage | 250 V |
| output | (Permanent) |

Ex level General

| | |
|---------------|-------|
| Rated voltage | 275 V |
|---------------|-------|

Ex connection data General

| | |
|------------------------------|---|
| Nominal cross section | 4 mm ² |
| Rated cross section AWG | 12 |
| Connection capacity rigid | 0.2 mm ² ... 6 mm ² |
| Connection capacity AWG | 24 ... 10 |
| Connection capacity flexible | 0.2 mm ² ... 4 mm ² |
| Connection capacity AWG | 24 ... 12 |
| output | (Permanent) |

Ex level Level 2

| | |
|----------------------|--------------------------------|
| Rated current | 29 A (4 mm ²) |
| Maximum load current | 32 A (6 mm ²) |
| Contact resistance | 0.9 mΩ |
| Temperature increase | 40 K (29 A/4 mm ²) |
| output | (Permanent) |

Ex level Level 3

| | |
|----------------------|----------------------------|
| Rated current | 6.3 A (4 mm ²) |
| Maximum load current | 6.3 A (6 mm ²) |
| Contact resistance | 5 mΩ |

Dimensions

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block



3002611

<https://www.phoenixcontact.com/us/products/3002611>

| | |
|--------------------|----------|
| Width | 6.2 mm |
| Height | 118.5 mm |
| Depth | 82.6 mm |
| Depth on NS 35/7,5 | 83.9 mm |
| Depth on NS 35/15 | 91.4 mm |

Material specifications

| | |
|---|------------------|
| Color | black (RAL 9005) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

Mechanical data

| | |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

Environmental and real-life conditions

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Spectrum | Long life test category 1, class B, body mounted |
| Frequency | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$ |
| ASD level | 0.964 (m/s ²)/Hz |
| Acceleration | 0.58g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|----------------|-------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape | Half-sine |
| Acceleration | 5g |
| Shock duration | 30 ms |

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block



3002611

<https://www.phoenixcontact.com/us/products/3002611>

| | |
|--------------------------------|-----------------------------------|
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-3 |
| | IEC 60947-7-3 |

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block

3002611

<https://www.phoenixcontact.com/us/products/3002611>

Drawings

Application drawing



Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block

3002611

<https://www.phoenixcontact.com/us/products/3002611>

Application drawing



Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block

3002611

<https://www.phoenixcontact.com/us/products/3002611>

Circuit diagram



PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block





3002611


<https://www.phoenixcontact.com/us/products/3002611>

Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3002611>


 **CSA**
Approval ID: 158887

 **EAC**
Approval ID: RU C-DE.BL08.B.00644

 **cULus Recognized**
Approval ID: E60425


| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------------|-----------------------|-----------------------|-------------------|-----------------------------|
| B | | | | |
| upper level | 300 V | 6.3 A | 24 - 10 | - |
| lower level | 300 V | 20 A | 24 - 10 | - |
| C | | | | |
| upper level | 300 V | 6.3 A | 24 - 10 | - |
| lower level | 300 V | 20 A | 24 - 10 | - |
| D | | | | |
| | 600 V | 5 A | 24 - 10 | - |

 **CSA**
Approval ID: 13631

 **cUL Recognized**
Approval ID: E192998

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| Feed-through | 275 V | 20 A | 24 - 10 | - |
| depending on the LED display | 275 V | 6.3 A | 24 - 10 | - |

 **IECEx**
Approval ID: IECExKIWA17.0025U

 **UL Recognized**
Approval ID: E192998

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|--------------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| Feed-through | 275 V | 20 A | 24 - 10 | - |

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block



3002611

<https://www.phoenixcontact.com/us/products/3002611>

| | | | | |
|------------------------------|-------|-------|---------|---|
| depending on the LED display | 275 V | 6.3 A | 24 - 10 | - |
|------------------------------|-------|-------|---------|---|



CCC

Approval ID: 2020322313000626



ATEX

Approval ID: KIWA17ATEX0045U



UKCA-EX

Approval ID: CSAE 21UKEX3605U



EAC Ex

Approval ID: KZ 7500525010101950

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block



3002611

<https://www.phoenixcontact.com/us/products/3002611>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250113 |
| ECLASS-15.0 | 27250113 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000899 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PT 4-L/HESILED 60 (5X20) - Fuse modular terminal block



3002611

<https://www.phoenixcontact.com/us/products/3002611>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com