

DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block



3034264

<https://www.phoenixcontact.com/us/products/3034264>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse terminal block for cartridge fuse insert, cross section: 0.5-10 mm², AWG: 20-8, width: 12.2 mm, color: Black

Commercial data

Item number	3034264
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE22
Product key	BE2235
GTIN	4046356052818
Weight per piece (including packing)	26.318 g
Weight per piece (excluding packing)	25.047 g
Customs tariff number	85369095
Country of origin	PL

DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block



3034264

<https://www.phoenixcontact.com/us/products/3034264>

Technical data

Notes

Order information:	Fuse-link not supplied as standard
--------------------	------------------------------------

Product properties

Product type	Fuse terminal block
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Fuse type	Glass / ceramics / ...
Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.77 W
Fuse	G / 5 x 20
LED voltage range	110 V AC ... 250 V AC
LED current range	0.5 mA ... 2.5 mA

Input data

LED voltage range	110 V AC ... 250 V AC
-------------------	-----------------------

Connection data

Number of connections per level	2
Nominal cross section	2.5 mm ²

Level 1 above 1

Connection method	Leg spring connection
Stripping length	12 mm
Internal cylindrical gage	A5
Connection in acc. with standard	IEC 60947-7-3
Conductor cross-section rigid	0.5 mm ² ... 10 mm ²
Cross section AWG	20 ... 8 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 6 mm ²
Conductor cross-section, flexible [AWG]	20 ... 10 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 6 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 6 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1.5 mm ²
Nominal cross section	1.5 mm ²
Nominal current	10 A

DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block



3034264

<https://www.phoenixcontact.com/us/products/3034264>

Maximum load current	10 A (with 4 mm ² conductor cross-section)
Nominal voltage	500 V

Level 1 below 1

Connection method	Leg spring connection
Stripping length	10 mm
Internal cylindrical gage	A3
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Cross section AWG	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 2.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 2.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ²
Nominal cross section	1.5 mm ²
Nominal current	10 A
Maximum load current	10 A
Nominal voltage	500 V

Dimensions

Width	12.2 mm
Height	71.5 mm
Depth on NS 35/7,5	51.3 mm
Depth on NS 35/15	58.8 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block



3034264

<https://www.phoenixcontact.com/us/products/3034264>

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-3
	IEC 60947-7-1

Mounting

Mounting type	NS 35/7,5
	NS 35/7,5

DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block

3034264

<https://www.phoenixcontact.com/us/products/3034264>

Drawings

Application drawing



Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks

DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block

3034264

<https://www.phoenixcontact.com/us/products/3034264>

Application drawing




Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks

DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block

3034264

<https://www.phoenixcontact.com/us/products/3034264>

Circuit diagram



DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block



3034264

<https://www.phoenixcontact.com/us/products/3034264>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3034264>



IECEE CB Scheme
Approval ID: NL-23160



EAC
Approval ID: RU C-DE.BL08.B.00644



KEMA-KEUR
Approval ID: 71-104946



EAC
Approval ID: KZ7500651131219505



cULus Recognized
Approval ID: E60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
Output	600 V	10 A	24 - 12	-
Input	600 V	10 A	20 - 8	-
C				
Output	600 V	10 A	24 - 12	-
Input	600 V	10 A	20 - 8	-

DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block



3034264

<https://www.phoenixcontact.com/us/products/3034264>

Classifications

ECLASS

ECLASS-13.0	27250113
ECLASS-15.0	27250113

ETIM

ETIM 10.0	EC000899
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DT 6/2,5-DREHSILA 250 (5X20) - Fuse modular terminal block



3034264

<https://www.phoenixcontact.com/us/products/3034264>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.31 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com