

# STME 6-BE - Component terminal block



3035688

<https://www.phoenixcontact.com/us/products/3035688>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component terminal block, If several diode terminal blocks need adding to the DIN rail, a spacer plate must be placed between them., for installing components that can be individually selected, nom. voltage: 500 V, nominal current: 30 A, connection method: Spring-cage connection, Rated cross section: 6 mm<sup>2</sup>, cross section: 0.2 mm<sup>2</sup> - 10 mm<sup>2</sup>, color: gray

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3035688       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE02          |
| Product key                          | BE2171        |
| GTIN                                 | 4046356743655 |
| Weight per piece (including packing) | 21.598 g      |
| Weight per piece (excluding packing) | 21.598 g      |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# STME 6-BE - Component terminal block



3035688

<https://www.phoenixcontact.com/us/products/3035688>

## Technical data

### Product properties

|                       |                          |
|-----------------------|--------------------------|
| Product type          | Component terminal block |
| Number of connections | 2                        |
| Number of rows        | 1                        |
| Potentials            | 1                        |

### Electrical properties

|   |        |
|---|--------|
| Maximum power dissipation for nominal condition | 1.31 W |
|---|--------|

### Connection data

|   |   |
|---|---|
| Number of connections per level   | 2   |
| Nominal cross section   | 6 mm <sup>2</sup>                                       |
| Connection method   | Spring-cage connection                                  |
| Stripping length  | 12 mm   |
| Internal cylindrical gage   | A4  |
| Conductor cross-section rigid   | 0.2 mm <sup>2</sup> ... 10 mm <sup>2</sup>              |
| Cross section AWG   | 24 ... 8 (converted acc. to IEC)                        |
| Conductor cross-section flexible  | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>               |
| Conductor cross-section, flexible [AWG]   | 24 ... 10 (converted acc. to IEC)                       |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.25 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.25 mm <sup>2</sup> ... 6 mm <sup>2</sup>              |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>             |
| Nominal cross section   | 6 mm <sup>2</sup>                                       |
| Nominal current   | 30 A (the current is determined by the component used)  |
| Nominal voltage   | 500 V (the voltage is determined by the component used) |

### Dimensions

|                    |          |
|--------------------|----------|
| Width              | 8.2 mm   |
| Height             | 100.8 mm |
| Depth on NS 35/7,5 | 60 mm    |
| Depth on NS 35/15  | 67.5 mm  |

### Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |

# STME 6-BE - Component terminal block



3035688

<https://www.phoenixcontact.com/us/products/3035688>

|   |             |
|---|-------------|
| Fire protection for rail vehicles (DIN EN 45545-2) R23  | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24  | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26  | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354)        | 28 MJ/kg    |
| Surface flammability NFPA 130 (ASTM E 162)              | passed      |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed      |
| Smoke gas toxicity NFPA 130 (SMP 800C)                  | passed      |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |


# STME 6-BE - Component terminal block

3035688

<https://www.phoenixcontact.com/us/products/3035688>

## Drawings

Circuit diagram



Circuit diagram




# STME 6-BE - Component terminal block



3035688

<https://www.phoenixcontact.com/us/products/3035688>

Circuit diagram



# STME 6-BE - Component terminal block



3035688

<https://www.phoenixcontact.com/us/products/3035688>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3035688>



**EAC**

Approval ID: RU C-DE.BL08.B.00644



**EAC**

Approval ID: KZ7500651131219505

# STME 6-BE - Component terminal block



3035688

<https://www.phoenixcontact.com/us/products/3035688>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250114 |
| ECLASS-15.0 | 27250114 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000898 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# STME 6-BE - Component terminal block



3035688

<https://www.phoenixcontact.com/us/products/3035688>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |              |
|---------|--------------|
| CO2e kg | 0.12 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)