


# ST 2,5-PE/L/N - Multi-level terminal block



3036084

<https://www.phoenixcontact.com/us/products/3036084>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multi-level terminal block, nom. voltage: 500 V, nominal current: 22 A, number of connections: 6, connection method: Spring-cage connection, Rated cross section: 2.5 mm<sup>2</sup>, 1st, 2nd and 3rd level, cross section: 0.08 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: gray

## Your advantages

- Simple wiring of very small, flexible conductors
- No restriction on cross-sections when using conductors with ferrules
- Meet the requirements of DIN EN 60947-7-2 or IEC 60947-7-2 for protective conductor connections
- High level of safety thanks to the low-resistance connection to the ground potential via the top-hat rail
- Direct contacting with the DIN rail enables fast, error-free grounding without additional wiring effort.
- Full flexibility thanks to the standardized CLIPLINE complete bridging, marking, and testing accessories

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3036084       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE02          |
| Product key                          | BE2125        |
| GTIN                                 | 4017918876579 |
| Weight per piece (including packing) | 20.088 g      |
| Weight per piece (excluding packing) | 20 g          |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# ST 2,5-PE/L/N - Multi-level terminal block



3036084

<https://www.phoenixcontact.com/us/products/3036084>

## Technical data

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | Ground terminal block |
| Product family        | ST                    |
| Number of connections | 6                     |
| Number of rows        | 3                     |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 0.77 W |

### Connection data

|                                 |                     |
|---------------------------------|---------------------|
| Grounding foot                  | Yes                 |
| Number of connections per level | 2                   |
| Nominal cross section           | 2.5 mm <sup>2</sup> |

### 1st, 2nd and 3rd level

|   |  |
|---|--|
| Connection method   | Spring-cage connection   |
| Note  | Please observe the current carrying capacity of the DIN rails. |
| Stripping length  | 8 mm ... 10 mm   |
| Internal cylindrical gage   | A3   |
| Connection in acc. with standard  | IEC 60947-7-1/IEC 60947-7-2                                    |
| Conductor cross-section rigid   | 0.08 mm <sup>2</sup> ... 4 mm <sup>2</sup>                     |
| Cross section AWG   | 28 ... 12 (converted acc. to IEC)                              |
| Conductor cross-section flexible  | 0.08 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                   |
| Conductor cross-section, flexible [AWG]   | 28 ... 14 (converted acc. to IEC)                              |
| Conductor cross-section flexible ultrasound-compressed                                    | 0.34 mm <sup>2</sup> ... 4 mm <sup>2</sup>                     |
| Conductor cross-section, flexible [AWG] ultrasound-compressed                             | 22 ... 12 (converted acc. to IEC)                              |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                   |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                   |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup>  |
| Nominal cross section   | 2.5 mm <sup>2</sup>  |
| Nominal current   | 22 A   |
| Maximum load current  | 28 A (with 4 mm <sup>2</sup> conductor cross-section)          |
| Nominal voltage   | 500 V  |

### Dimensions

|                 |        |
|-----------------|--------|
| Width           | 5.2 mm |
| End cover width | 2.2 mm |

# ST 2,5-PE/L/N - Multi-level terminal block



3036084

<https://www.phoenixcontact.com/us/products/3036084>

|                    |         |
|--------------------|---------|
| Height             | 99.5 mm |
| Depth on NS 35/7,5 | 58 mm   |
| Depth on NS 35/15  | 65.5 mm |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group   | I               |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

|                                  |                             |
|----------------------------------|-----------------------------|
| Connection in acc. with standard | IEC 60947-7-1/IEC 60947-7-2 |
|----------------------------------|-----------------------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# ST 2,5-PE/L/N - Multi-level terminal block




3036084

<https://www.phoenixcontact.com/us/products/3036084>

## Drawings

Circuit diagram



# ST 2,5-PE/L/N - Multi-level terminal block





3036084


<https://www.phoenixcontact.com/us/products/3036084>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3036084>

|  <b>CSA</b><br>Approval ID: 158887 |                       |                       |                   |                      |
|---|-----------------------|-----------------------|-------------------|----------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| <b>B</b>  |                       |                       |                   |                      |
|   | 300 V                 | 20 A                  | 28 - 12           | -                    |
| PE connection   | -                     | -                     | 28 - 12           | -                    |
| <b>C</b>  |                       |                       |                   |                      |
|   | 300 V                 | 20 A                  | 28 - 12           | -                    |
| PE connection   | -                     | -                     | 28 - 12           | -                    |
| <b>D</b>  |                       |                       |                   |                      |
|   | 600 V                 | 5 A                   | 28 - 12           | -                    |
| PE connection   | -                     | -                     | 28 - 12           | -                    |

|  <b>EAC</b><br>Approval ID: RU C-DE.BL08.B.00644 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| <b>B</b>   |                       |                       |                   |                      |
|  | 300 V                 | 20 A                  | 28 - 12           | -                    |
| PE connection  | -                     | -                     | 28 - 12           | -                    |
| <b>C</b>   |                       |                       |                   |                      |
|  | 300 V                 | 20 A                  | 28 - 12           | -                    |
| PE connection  | -                     | -                     | 28 - 12           | -                    |
| <b>F</b>   |                       |                       |                   |                      |
|  | 500 V                 | 20 A                  | 28 - 12           | -                    |
| <b>D</b>   |                       |                       |                   |                      |
| PE connection  | -                     | -                     | 28 - 12           | -                    |

|  <b>EAC</b><br>Approval ID: KZ7500651131219505 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

# ST 2,5-PE/L/N - Multi-level terminal block



3036084

<https://www.phoenixcontact.com/us/products/3036084>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250104 |
| ECLASS-15.0 | 27250104 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000901 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# ST 2,5-PE/L/N - Multi-level terminal block



3036084

<https://www.phoenixcontact.com/us/products/3036084>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.115 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)