

PS-6/2,3MM RD - Test plug



3038736

<https://www.phoenixcontact.com/us/products/3038736>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Test plug, number of positions: 1, color: red



Your advantages

- Housing for test plugs, any combination
- The test plugs are inserted in the function shaft of the terminal blocks from the CLIPLINE complete system or in the test pick-offs provided

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3038736 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE29 |
| Product key | BE2Z3X |
| GTIN | 4017918904166 |
| Weight per piece (including packing) | 1.43 g |
| Weight per piece (excluding packing) | 1.18 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

PS-6/2,3MM RD - Test plug



3038736

<https://www.phoenixcontact.com/us/products/3038736>

Technical data

Product properties

| | |
|---------------------|--------------------------|
| Product type | Test plug terminal block |
| Number of positions | 1 |
| Pitch | 6 mm |

Connection data

| | |
|-------------------|------------------------|
| Connection method | Spring-cage connection |
|-------------------|------------------------|

Dimensions

| | |
|--------------------|--------|
| Width | 6.2 mm |
| Height | 14 mm |
| Depth on NS 35/7,5 | 36 mm |
| Pitch | 6 mm |

Material specifications

| | |
|--|----------------|
| Color | red (RAL 3001) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C () |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

PS-6/2,3MM RD - Test plug

3038736

<https://www.phoenixcontact.com/us/products/3038736>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250304 |
| ECLASS-15.0 | 27250304 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002555 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 20122000 |
|-------------|----------|

PS-6/2,3MM RD - Test plug



3038736

<https://www.phoenixcontact.com/us/products/3038736>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.062 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com