

# PS-7,5/2,3MM RD - Test plug

3038749

<https://www.phoenixcontact.com/us/products/3038749>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, number of positions: 1, color: red

## Your advantages

- The test plug reliably makes contact in the bridge shaft and in all test sockets with a 2.3 mm or 4 mm diameter
- Individual test adapters can be combined using the modular PS-...2,3MM test plug.
- The test plugs are inserted in the function shaft of the terminal blocks from the CLIPLINE complete system or in the test pick-offs provided
- Housing for test plugs, any combination

## Commercial data

Item number	3038749
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4017918904159
Weight per piece (including packing)	1.47 g
Weight per piece (excluding packing)	1.25 g
Customs tariff number	85366990
Country of origin	DE

# PS-7,5/2,3MM RD - Test plug



3038749

<https://www.phoenixcontact.com/us/products/3038749>

## Technical data

### Product properties

Product type	Test plug terminal block
Number of positions	1
Pitch	7.5 mm

### Connection data

Connection method	Spring-cage connection
-------------------	------------------------

### Dimensions

Width	7.5 mm
Height	14 mm
Depth on NS 35/7,5	36 mm
Pitch	7.5 mm

### Material specifications

Color	red (RAL 3001)
Material	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C ( )
Permissible humidity (storage/transport)	30 % ... 70 %

# PS-7,5/2,3MM RD - Test plug



3038749

<https://www.phoenixcontact.com/us/products/3038749>

## Classifications

### ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

### ETIM

ETIM 10.0	EC002555
-----------	----------

### UNSPSC

UNSPSC 21.0	20122000
-------------	----------

# PS-7,5/2,3MM RD - Test plug



3038749

<https://www.phoenixcontact.com/us/products/3038749>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.078 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)