

PAI-ST 35/1000MM - Test adapter



3029994

<https://www.phoenixcontact.com/us/products/3029994>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test adapter, number of positions: 1, color: red

Product description

Test adapter, with molded cable, 1 meter long

Commercial data

Item number	3029994
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4046356662239
Weight per piece (including packing)	37.075 g
Weight per piece (excluding packing)	37.075 g
Customs tariff number	85444290
Country of origin	PL

Technical data

Product properties

Product type	Test socket
Number of positions	1

Electrical properties

Nominal current I_N	24 A
-----------------------	------

Connection data

Connection method	Plug-in connection
Conductor cross-section flexible	2.5 mm ² ...

Dimensions

Width	6.9 mm
Height	10.8 mm
Depth	56.9 mm

Material specifications

Color	red (RAL 3001)
Material	PA
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

PAI-ST 35/1000MM - Test adapter



3029994

<https://www.phoenixcontact.com/us/products/3029994>

Classifications

ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

ETIM

ETIM 10.0	EC002555
-----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

PAI-ST 35/1000MM - Test adapter



3029994

<https://www.phoenixcontact.com/us/products/3029994>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com