

FBS 1/3/5/7/9/11-5 - Plug-in bridge



3030375

<https://www.phoenixcontact.com/us/products/3030375>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in bridge, pitch: 5.2 mm, number of positions: 11, nominal current: 24 A, pin assignment: 1,3,5,7,9,11, color: red

Your advantages

- The 2- to 50-pos. jumpers can bridge up to 50 terminal blocks in the two bridge shafts of the CLIPLINE complete system in one step

Commercial data

Item number	3030375
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z2X
GTIN	4046356707039
Weight per piece (including packing)	7.73 g
Weight per piece (excluding packing)	7.6 g
Customs tariff number	85366990
Country of origin	PL

Technical data

Notes

Note on application	Version with single- or double-sided cutting edge. Please keep in mind the possible impact on touch protection as well as air clearances and creepage distances.
---------------------	--

Product properties

Product type	Plug-in bridge
Number of positions	11
Pitch	5.2 mm

Electrical properties

Maximum load current	24 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Connection data

Maximum load current	24 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Dimensions

Pitch	5.2 mm
-------	--------

Material specifications

Color	red (RAL 3001)
Material	Copper
Flammability rating according to UL 94	V0
Insulating material	PA

Mechanical properties

Technical data

Pin assignment	1, 3, 5, 7, 9, 11
----------------	-------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %

FBS 1/3/5/7/9/11-5 - Plug-in bridge



3030375

<https://www.phoenixcontact.com/us/products/3030375>

Permissible humidity (storage/transport)	30 % ... 70 %
--	---------------

Mounting

Mounting type	Plug-in mounting
---------------	------------------

FBS 1/3/5/7/9/11-5 - Plug-in bridge



3030375

<https://www.phoenixcontact.com/us/products/3030375>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBS 1/3/5/7/9/11-5 - Plug-in bridge



3030375

<https://www.phoenixcontact.com/us/products/3030375>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com