

PAI 1,5/4-F - Test adapter



3032826

<https://www.phoenixcontact.com/us/products/3032826>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test adapter, Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in, 4 mm test adapter, for terminal blocks with 4.2 mm, 5.2 mm, and 6.2 mm pitch, number of positions: 1, color: gray

Your advantages

- Make contact and latch securely to any point in the function shaft
- Test adapter for accommodating safety test plugs with a 4 mm diameter

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3032826 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE29 |
| Product key | BE2Z3X |
| GTIN | 4046356516396 |
| Weight per piece (including packing) | 2.4 g |
| Weight per piece (excluding packing) | 2.35 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

PAI 1,5/4-F - Test adapter



3032826

<https://www.phoenixcontact.com/us/products/3032826>

Technical data

Product properties

| | |
|---------------------|-------------|
| Product type | Test socket |
| Number of positions | 1 |

Electrical properties

| | |
|----------------------|-------|
| Maximum load current | 10 A |
| Max. voltage | 250 V |

Connection data

| | |
|----------------------|--------------------|
| Maximum load current | 10 A |
| Connection method | Plug-in connection |

Dimensions

| | |
|--------------|---------|
| Width | 5.8 mm |
| Height | 5.8 mm |
| Depth | 51.5 mm |
| Diameter | 5.8 mm |
| Pin diameter | 2.4 mm |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Material | Copper |
| Flammability rating according to UL 94 | V0 |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |

PAI 1,5/4-F - Test adapter

3032826

<https://www.phoenixcontact.com/us/products/3032826>



| | |
|--|---------------|
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

PAI 1,5/4-F - Test adapter

3032826

<https://www.phoenixcontact.com/us/products/3032826>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250304 |
| ECLASS-15.0 | 27250304 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002555 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 20122000 |
|-------------|----------|

PAI 1,5/4-F - Test adapter

3032826

<https://www.phoenixcontact.com/us/products/3032826>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 9.292 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com