


# STTBU 4-PV - Double-level terminal block



3033184

<https://www.phoenixcontact.com/us/products/3033184>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Double-level terminal block, with equipotential bonder, nom. voltage: 500 V, nominal current: 30 A, connection method: Spring-cage connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.08 mm<sup>2</sup> - 6 mm<sup>2</sup>, connection method: Screw connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 6 mm<sup>2</sup>, mounting: NS 35/7,5, NS 35/15, color: gray

## Your advantages

- For a clear overview, each terminal point can be labeled
- Can be bridged in both levels to implement different switching tasks
- Can be consistently bridged to the STTB 4 standard double-level terminal blocks

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 3033184                        |
| Packing unit                         | 50 pc                          |
| Minimum order quantity               | 50 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BE02                           |
| Product key                          | BE2119                         |
| GTIN                                 | 4046356148177                  |
| Weight per piece (including packing) | 19.311 g                       |
| Weight per piece (excluding packing) | 19.311 g                       |
| Customs tariff number                | 85369010                       |
| Country of origin                    | PL                             |

# STTBU 4-PV - Double-level terminal block



3033184

<https://www.phoenixcontact.com/us/products/3033184>

## Technical data

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | Hybrid terminal block |
| Number of connections | 4                     |
| Number of rows        | 2                     |
| Potentials            | 1                     |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 1.02 W |

### Connection data

|                                 |                   |
|---------------------------------|-------------------|
| Number of connections per level | 2                 |
| Nominal cross section           | 4 mm <sup>2</sup> |

#### Level 1+2 above 1

|   |  |
|---|--|
| Connection method   | Spring-cage connection   |
| Stripping length  | 8 mm ... 10 mm   |
| Connection in acc. with standard  | IEC 60947-7-1  |
| Conductor cross-section rigid   | 0.08 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Cross section AWG   | 28 ... 10 (converted acc. to IEC)  |
| Conductor cross-section flexible  | 0.08 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG]   | 28 ... 12 (converted acc. to IEC)  |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup>  |
| Nominal cross section   | 4 mm <sup>2</sup>  |
| Nominal current   | 30 A   |
| Maximum load current  | 36 A (The maximum load current must not be exceeded by the total current of all connected conductors.) |
| Nominal voltage   | 500 V  |

#### Level 1+2 below 1

|                                  |                  |
|----------------------------------|------------------|
| Connection method                | Screw connection |
| Screw thread                     | M3               |
| Tightening torque                | 0.6 ... 0.8 Nm   |
| Stripping length                 | 8 mm ... 10 mm   |
| Internal cylindrical gage        | A4               |
| Connection in acc. with standard | IEC 60947-7-1    |

# STTBU 4-PV - Double-level terminal block



3033184

<https://www.phoenixcontact.com/us/products/3033184>

|   |   |
|---|---|
| Conductor cross-section rigid   | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>                |
| Cross section AWG   | 26 ... 10 (converted acc. to IEC)                         |
| Conductor cross-section flexible  | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>                |
| Conductor cross-section, flexible [AWG]   | 26 ... 10 (converted acc. to IEC)                         |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>                |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>                |
| 2 conductors with same cross section, rigid   | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>              |
| 2 conductors with same cross section, flexible  | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>              |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>              |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>               |
| Nominal cross section   | 4 mm <sup>2</sup>   |
| Nominal current   | 30 A (with 4 mm <sup>2</sup> conductor cross-section)     |
| Maximum load current  | 36 A (with 6 mm <sup>2</sup> conductor cross-section)     |
|   | 30 A (with 4 mm <sup>2</sup> conductor cross-section)     |
|   | 22 A (with a 2.5 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage   | 500 V   |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| End cover width    | 2.2 mm  |
| Height             | 81 mm   |
| Depth on NS 35/7,5 | 55.5 mm |
| Depth on NS 35/15  | 63 mm   |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group   | I               |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Electrical tests

# STTBU 4-PV - Double-level terminal block



3033184

<https://www.phoenixcontact.com/us/products/3033184>

## Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 7.3 kV      |
| Result                | Test passed |

## Temperature-rise test

|  |                                     |
|--|-------------------------------------|
| Requirement temperature-rise test              | Increase in temperature $\leq 45$ K |
| Result   | Test passed                         |
| Short-time withstand current 4 mm <sup>2</sup> | 0.48 kA                             |
| Short-time withstand current 6 mm <sup>2</sup> | 0.72 kA                             |
| Result   | Test passed                         |

## Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 1.89 kV     |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35       |
| Test force setpoint     | 1 N         |
| Result                  | Test passed |

### Test for conductor damage and slackening

|                                |                               |
|--------------------------------|-------------------------------|
| Rotation speed                 | 10 rpm                        |
| Revolutions                    | 135                           |
| Conductor cross-section/weight | 0.14 mm <sup>2</sup> / 0.2 kg |
|                                | 4 mm <sup>2</sup> / 0.9 kg    |
|                                | 6 mm <sup>2</sup> / 1.4 kg    |
| Result                         | Test passed                   |

### Test for conductor damage and slackening

|                                |                               |
|--------------------------------|-------------------------------|
| Rotation speed                 | 10 rpm                        |
| Revolutions                    | 135                           |
| Conductor cross-section/weight | 0.08 mm <sup>2</sup> / 0.1 kg |
|                                | 4 mm <sup>2</sup> / 0.9 kg    |
|                                | 6 mm <sup>2</sup> / 1.4 kg    |
| Result                         | Test passed                   |

## Environmental and real-life conditions

# STTBU 4-PV - Double-level terminal block



3033184

<https://www.phoenixcontact.com/us/products/3033184>

## Aging

|                    |             |
|--------------------|-------------|
| Temperature cycles | 192         |
| Result             | Test passed |

## Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

## Oscillation/broadband noise

|                        |  |
|------------------------|--|
| Specification          | DIN EN 50155 (VDE 0115-200):2008-03              |
| Spectrum               | Long life test category 1, class B, body mounted |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$   |
| ASD level              | $1.857 \text{ (m/s}^2\text{)/Hz}$                |
| Acceleration           | 0.8g   |
| Test duration per axis | 5 h  |
| Test directions        | X-, Y- and Z-axis                                |
| Result                 | Test passed                                      |

## Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 5g                                  |
| Shock duration                 | 30 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

## Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|                                  | IEC 60947-7-1 |

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# STTBU 4-PV - Double-level terminal block




3033184

<https://www.phoenixcontact.com/us/products/3033184>

## Drawings

Circuit diagram



# STTBU 4-PV - Double-level terminal block



3033184

<https://www.phoenixcontact.com/us/products/3033184>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3033184>



**EAC**

Approval ID: RU C-DE.BL08.B.00644



**EAC**

Approval ID: KZ7500651131219505

# STTBU 4-PV - Double-level terminal block



3033184

<https://www.phoenixcontact.com/us/products/3033184>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250201 |
| ECLASS-15.0 | 27250201 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# STTBU 4-PV - Double-level terminal block



3033184

<https://www.phoenixcontact.com/us/products/3033184>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 31f4cced-d8f9-4119-b2d8-dbbd0682a249 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)