

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover profile, for covering terminal strips, snapped onto APT-ME cover profile carrier or APH-ME end bracket. A cover profile carrier should be positioned at the ends and at intervals of around 40 cm. Length supplied: 1 m

Your advantages

- The cover can be securely snapped onto the corresponding APH-ME end brackets and sealed as an option
- Cover profiles provide protection against unauthorized actuation of terminal strips
- This profile has been specially adapted to the shape of the test disconnect terminal blocks

Commercial data


| | |
|--------------------------------------|---------------|
| Item number | 3034361 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE06 |
| Product key | BE61ZX |
| GTIN | 4046356316774 |
| Weight per piece (including packing) | 540 g |
| Weight per piece (excluding packing) | 540 g |
| Customs tariff number | 39162000 |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Cover profile |
|--------------|---------------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 142 mm |
| Height | 1000 mm |
| Depth | 48.4 mm |
| Length | 1000 mm |

Material specifications

| | |
|--|-------------|
| Color | transparent |
| Material | PVC |
| Flammability rating according to UL 94 | V0 |


Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -15 °C ... 65 °C |
|---------------------------------|------------------|

Drawings

Dimensional drawing



3034361

<https://www.phoenixcontact.com/us/products/3034361>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27250190 |
| ECLASS-13.0 | 27141190 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002848 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|