

# UT 4/ 1P - Feed-through terminal block

3045583

<https://www.phoenixcontact.com/us/products/3045583>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 800 V, nominal current: 32 A, number of connections: 2, connection method: Screw/plug-in connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 6 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: gray

## Your advantages

- Terminal blocks that can be connected on both sides available
- Compatible with standard UT terminal blocks
- Uniform, touch-proof plug-in zone

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3045583       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1141        |
| GTIN                                 | 4046356083096 |
| Weight per piece (including packing) | 9.17 g        |
| Weight per piece (excluding packing) | 8.46 g        |
| Customs tariff number                | 85369010      |
| Country of origin                    | TR            |

# UT 4/ 1P - Feed-through terminal block



3045583

<https://www.phoenixcontact.com/us/products/3045583>

## Technical data

### Notes

#### General

|      |   |
|------|---|
| Note | With a free-hanging connection, an insulating foil has to be placed between the plug connection and electrically conductive surfaces. |
|------|---|

### Product properties

|                       |                        |
|-----------------------|------------------------|
| Product type          | Plug-in terminal block |
| Product family        | UT                     |
| Number of connections | 2                      |
| Number of rows        | 1                      |
| Potentials            | 1                      |

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 1.02 W |

### Connection data

|                                 |                   |
|---------------------------------|-------------------|
| Number of connections per level | 2                 |
| Nominal cross section           | 4 mm <sup>2</sup> |

#### Level 1 below 1

|   |  |
|---|--|
| Connection method   | Screw/plug-in connection                     |
| Screw thread  | M3   |
| Tightening torque   | 0.6 ... 0.8 Nm                               |
| Stripping length  | 9 mm   |
| Internal cylindrical gage   | A4   |
| Connection in acc. with standard  | IEC 61984                                    |
| Conductor cross-section rigid   | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Cross section AWG   | 26 ... 10 (converted acc. to IEC)            |
| Conductor cross-section flexible  | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG]   | 26 ... 10 (converted acc. to IEC)            |
| Conductor cross-section flexible ultrasound-compressed  | 0.34 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG] ultrasound-compressed   | 22 ... 10 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve)   | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Flexible conductor cross-section (ferrule with plastic sleeve)  | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section flexible (2 conductors with the same cross-section, with TWIN ferrule and plastic sleeve) | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, rigid   | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |

# UT 4/ 1P - Feed-through terminal block



3045583

<https://www.phoenixcontact.com/us/products/3045583>

|   |   |
|---|---|
| 2 conductors with same cross section, flexible  | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>          |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>          |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>           |
| Nominal cross section   | 4 mm <sup>2</sup>                                     |
| Nominal current   | 32 A  |
| Maximum load current  | 32 A (with 6 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage   | 800 V   |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| End cover width    | 2.2 mm  |
| Height             | 47.6 mm |
| Depth on NS 35/7,5 | 47.5 mm |
| Depth on NS 35/15  | 55 mm   |

## Material specifications

|  |                 |
|--|-----------------|
| Color  | gray (RAL 7042) |
| Flammability rating according to UL 94                           | V0              |
| Insulating material group  | I               |
| Insulating material  | PA              |
| Static insulating material application in cold                   | -60 °C          |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26           | HL 1 - HL 3     |
| Surface flammability NFPA 130 (ASTM E 162)                       | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)          | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                           | passed          |

## Electrical tests

|  |             |
|--|-------------|
| Short-time withstand current 4 mm <sup>2</sup> | 0.48 kA     |
| Short-time withstand current 6 mm <sup>2</sup> | 0.72 kA     |
| Result   | Test passed |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

# UT 4/ 1P - Feed-through terminal block



3045583

<https://www.phoenixcontact.com/us/products/3045583>

## Attachment on the carrier

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35       |
| Test force setpoint     | 1 N         |
| Result                  | Test passed |

## Test for conductor damage and slackening

|                                |                               |
|--------------------------------|-------------------------------|
| Rotation speed                 | 10 rpm                        |
| Revolutions                    | 135                           |
| Conductor cross-section/weight | 0.14 mm <sup>2</sup> / 0.3 kg |
|                                | 4 mm <sup>2</sup> / 0.9 kg    |
|                                | 6 mm <sup>2</sup> / 1.4 kg    |
| Result                         | Test passed                   |

## Environmental and real-life conditions

### Service life

|                             |     |
|-----------------------------|-----|
| Insertion/withdrawal cycles | 100 |
|-----------------------------|-----|

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |  |
|------------------------|--|
| Specification          | DIN EN 50155 (VDE 0115-200):2008-03              |
| Spectrum               | Long life test category 1, class B, body mounted |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$   |
| ASD level              | 0.02g <sup>2</sup> /Hz                           |
| Acceleration           | 0.8g   |
| Test duration per axis | 5 h  |
| Test directions        | X-, Y- and Z-axis                                |
| Result                 | Test passed                                      |

### Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 5g                                  |
| Shock duration                 | 30 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)         | -60 °C ... 100 °C (max. operating temperature range including self-heating, see derating curve) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)                       |
| Ambient temperature (assembly)          | -5 °C ... 70 °C   |

# UT 4/ 1P - Feed-through terminal block



3045583

<https://www.phoenixcontact.com/us/products/3045583>

|  |                 |
|--|-----------------|
| Ambient temperature (actuation)          | -5 °C ... 70 °C |
| Permissible humidity (operation)         | 20 % ... 90 %   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

## Standards and regulations

|                                  |           |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |


# UT 4/ 1P - Feed-through terminal block

3045583

<https://www.phoenixcontact.com/us/products/3045583>

## Drawings

Diagram



The figure shows the derating curve of the UT 4/1P... terminal block in connection with the UPVB 4 plug


# UT 4/ 1P - Feed-through terminal block

3045583

<https://www.phoenixcontact.com/us/products/3045583>



Circuit diagram



# UT 4/ 1P - Feed-through terminal block





3045583


<https://www.phoenixcontact.com/us/products/3045583>

## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3045583>

|  <b>IECEE CB Scheme</b><br>Approval ID: NL-34722_A1 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  |                       |                       |                   |                      |
|  | 800 V                 | 32 A                  | -                 | -                    |

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| B  |                       |                       |                   |                      |
|  | 600 V                 | 30 A                  | 26 - 10           | -                    |
| Multi-conductor connection   | 600 V                 | 30 A                  | 26 - 14           | -                    |
| C  |                       |                       |                   |                      |
|  | 600 V                 | 30 A                  | 26 - 10           | -                    |
| Multi-conductor connection   | 600 V                 | 30 A                  | 26 - 14           | -                    |

|  <b>KEMA-KEUR</b><br>Approval ID: 71-114072 REV.1 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  |                       |                       |                   |                      |
|  | 800 V                 | 32 A                  | -                 | -                    |

|  <b>EAC</b><br>Approval ID: KZ7500651131219505 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

|  <b>CSA</b><br>Approval ID: 13631 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| B  |                       |                       |                   |                      |
|  | 600 V                 | 30 A                  | 26 - 10           | -                    |
| C  |                       |                       |                   |                      |
|  | 600 V                 | 30 A                  | 26 - 10           | -                    |

# UT 4/ 1P - Feed-through terminal block



3045583

<https://www.phoenixcontact.com/us/products/3045583>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250117 |
| ECLASS-15.0 | 27250117 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UT 4/ 1P - Feed-through terminal block



3045583

<https://www.phoenixcontact.com/us/products/3045583>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 549545aa-9e29-487b-9a53-9c54ca7fff15 |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.028 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)