


# UT 4-MTL KNIFE-RD - Knife-disconnect terminal block



3046152

<https://www.phoenixcontact.com/us/products/3046152>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Knife-disconnect terminal block, with actuation latch, nom. voltage: 500 V, nominal current: 20 A, connection method: Screw connection, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 6 mm<sup>2</sup>, mounting: NS 35/7,5, NS 35/15, color: gray

## Your advantages

- Globally recognized: Internationally proven screw connection
- Maintenance-free and vibration-resistant thanks to the patented Reakdyn principle
- Convenient separation of circuits with the implemented lever-type disconnect knives
- Space savings and flexibility with the connection of two identical conductors
- Long-term stable connections with the use of high-quality materials
- Low self-heating due to high contact forces
- Maximum efficiency in the smallest space - thanks to integrated level bridging, the connections are connected across levels

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3046152       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1131        |
| GTIN                                 | 4055626063447 |
| Weight per piece (including packing) | 13.35 g       |
| Weight per piece (excluding packing) | 13.35 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# UT 4-MTL KNIFE-RD - Knife-disconnect terminal block



3046152

<https://www.phoenixcontact.com/us/products/3046152>

## Technical data

### Product properties

|                       |                           |
|-----------------------|---------------------------|
| Product type          | Disconnect terminal block |
| Product family        | UT                        |
| Area of application   | Machine building          |
|                       | Plant engineering         |
| Number of connections | 2                         |
| Number of rows        | 1                         |
| Potentials            | 1                         |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 1.02 W |

### Connection data

|                                 |                   |
|---------------------------------|-------------------|
| Number of connections per level | 2                 |
| Nominal cross section           | 4 mm <sup>2</sup> |

### Level 1 above 1 below 1

|   |  |
|---|--|
| Connection method   | Screw connection                             |
| Screw thread  | M3   |
| Tightening torque   | 0.6 ... 0.8 Nm                               |
| Stripping length  | 9 mm   |
| Internal cylindrical gage   | A4   |
| Connection in acc. with standard  | IEC 60947-7-1                                |
| Conductor cross-section rigid   | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Cross section AWG   | 26 ... 10 (converted acc. to IEC)            |
| Conductor cross-section flexible  | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG]   | 26 ... 10 (converted acc. to IEC)            |
| Conductor cross-section flexible ultrasound-compressed                                    | 0.34 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG] ultrasound-compressed                             | 22 ... 10 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| 2 conductors with same cross section, rigid   | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible  | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>  |
| Nominal cross section   | 2.5 mm <sup>2</sup>                          |

# UT 4-MTL KNIFE-RD - Knife-disconnect terminal block



3046152

<https://www.phoenixcontact.com/us/products/3046152>

|                      |   |
|----------------------|---|
| Nominal current      | 20 A  |
| Maximum load current | 20 A (with 6 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage      | 500 V   |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| Height             | 57.8 mm |
| Depth on NS 35/7,5 | 49.1 mm |
| Depth on NS 35/15  | 56.6 mm |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group   | I               |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 27,5 MJ/kg      |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

# UT 4-MTL KNIFE-RD - Knife-disconnect terminal block



3046152

<https://www.phoenixcontact.com/us/products/3046152>

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# UT 4-MTL KNIFE-RD - Knife-disconnect terminal block




3046152

<https://www.phoenixcontact.com/us/products/3046152>

## Drawings

Circuit diagram



# UT 4-MTL KNIFE-RD - Knife-disconnect terminal block




3046152


<https://www.phoenixcontact.com/us/products/3046152>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3046152>

 **CSA**  
Approval ID: 13631

 **EAC**  
Approval ID: KZ7500651131219505

 **cULus Recognized**  
Approval ID: E60425

|                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|----------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| <b>B</b>                   |                       |                       |                   |                             |
|                            | 600 V                 | 16 A                  | 26 - 10           | -                           |
| Multi-conductor connection | 600 V                 | 16 A                  | 26 - 14           | -                           |
| <b>C</b>                   |                       |                       |                   |                             |
|                            | 600 V                 | 16 A                  | 26 - 10           | -                           |
| Multi-conductor connection | 600 V                 | 16 A                  | 26 - 14           | -                           |

 **CSA**  
Approval ID: 13631

# UT 4-MTL KNIFE-RD - Knife-disconnect terminal block



3046152

<https://www.phoenixcontact.com/us/products/3046152>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-15.0 | 27250108 |
| ECLASS-13.0 | 27250108 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000902 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

3046152

<https://www.phoenixcontact.com/us/products/3046152>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | ee113a1b-84ad-4d0e-be6f-c6f1fc917522 |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.041 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)