

SB-ME 4-6 - Bridge bar

3035757

<https://www.phoenixcontact.com/us/products/3035757>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bridge bar, pitch: 6.2 mm, number of positions: 4, nominal current: 25 A, length: 21 mm, color: gray/orange

Your advantages

- Feed-through terminal blocks of the same shape are available
- Clear selection thanks to printed switching symbols
- Easy operation
- Clear
- Compact design
- Flexible and comprehensive accessories
- Reliably snapped into the end positions
- Contact made via screw terminal points

Commercial data

Item number	3035757
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z2X
GTIN	4046356521819
Weight per piece (including packing)	12.45 g
Weight per piece (excluding packing)	12.45 g
Customs tariff number	85366990
Country of origin	PL

SB-ME 4-6 - Bridge bar



3035757

<https://www.phoenixcontact.com/us/products/3035757>

Technical data

Product properties

Product type	Bridge bar
Number of positions	4
Pitch	6.2 mm
Potentials	1

Electrical properties

Maximum load current	25 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Connection data

Maximum load current	25 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Dimensions

Width	24.7 mm
Height	21.2 mm
Depth	36.4 mm
Length	21.2 mm
Pitch	6.2 mm

Material specifications

Color	multicolored (RAL -)
	gray (RAL 7042)
	orange (RAL 2003)
Material	Copper
Flammability rating according to UL 94	V0
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Plug-in mounting
---------------	------------------

SB-ME 4-6 - Bridge bar



3035757

<https://www.phoenixcontact.com/us/products/3035757>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SB-ME 4-6 - Bridge bar



3035757

<https://www.phoenixcontact.com/us/products/3035757>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.048 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com