

P-FU 6,3X32-EX - Fuse plug

3046499

<https://www.phoenixcontact.com/us/products/3046499>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse plug, nom. voltage: 500 V, nominal current: 10 A, connection method: Plug-in connection, fuse type: G / 6,3 x 32, color: black

Your advantages

- Large-surface labeling option
- Test contacts on both sides of the fuse
- Versions with bipolar error display
- Can be used for overload/short-circuit protection

Commercial data

Item number	3046499
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4046356919258
Weight per piece (including packing)	6.32 g
Weight per piece (excluding packing)	6.32 g
Customs tariff number	85369095
Country of origin	PL

P-FU 6,3X32-EX - Fuse plug



3046499

<https://www.phoenixcontact.com/us/products/3046499>

Technical data

Notes

Notes on operation	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
--------------------	---

Product properties

Product type	Fuse
Potentials	1

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Fuse	G / 6,3 x 32
------	--------------

Connection data

Connection method	Plug-in connection
Nominal current	10 A (the current is determined by the fuse used)
Maximum load current	10 A (the current is determined by the fuse used)
Nominal voltage	500 V (if used as fuse terminal block)
	500 V (if used as disconnect terminal block)

Dimensions

Width	8.2 mm
Height	40 mm
Depth	27 mm
Length	40 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

P-FU 6,3X32-EX - Fuse plug


3046499

<https://www.phoenixcontact.com/us/products/3046499>



Drawings

Application drawing



Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks


P-FU 6,3X32-EX - Fuse plug

3046499

<https://www.phoenixcontact.com/us/products/3046499>



Application drawing



Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks

P-FU 6,3X32-EX - Fuse plug





3046499


<https://www.phoenixcontact.com/us/products/3046499>


Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3046499>

 CSA Approval ID: 158887				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	10 A	-	-

 EAC Approval ID: RU C-DE.BL08.B.00714				
---	--	--	--	--

 cUL Recognized Approval ID: E192998				
---	--	--	--	--

 EAC Ex Approval ID: RU C-DE.Ax07.B.03227				
--	--	--	--	--

 UL Recognized Approval ID: E192998				
--	--	--	--	--

 CCC Approval ID: 2020322313000632				
---	--	--	--	--

 UKCA-EX Approval ID: UL22UKEX2452U				
--	--	--	--	--

P-FU 6,3X32-EX - Fuse plug



3046499

<https://www.phoenixcontact.com/us/products/3046499>

Classifications

ECLASS

ECLASS-13.0	27250305
ECLASS-15.0	27250305

ETIM

ETIM 10.0	EC002018
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

P-FU 6,3X32-EX - Fuse plug



3046499

<https://www.phoenixcontact.com/us/products/3046499>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.028 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com