

# DS-ST 4 - Cover segment

3036615

<https://www.phoenixcontact.com/us/products/3036615>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover segment, depth: 36.5 mm, height: 87 mm, color: gray



## Commercial data

Item number	3036615
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z1X
GTIN	4017918607357
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	0.881 g
Customs tariff number	85389099
Country of origin	DE

# DS-ST 4 - Cover segment



3036615

<https://www.phoenixcontact.com/us/products/3036615>

## Technical data

### Product properties

Product type	End cover
--------------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

### Dimensions

Height	87 mm
Depth	36.5 mm
Min. material thickness	1 mm

### Notes

General	A cover segment should be used if terminal blocks with a higher number of terminal points cannot be covered by the contour of another terminal block.
---------	---

# DS-ST 4 - Cover segment



3036615

<https://www.phoenixcontact.com/us/products/3036615>

## Classifications

### ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

### ETIM

ETIM 10.0	EC000886
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# DS-ST 4 - Cover segment



3036615

<https://www.phoenixcontact.com/us/products/3036615>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.028 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)