

AGK 4-UT 10 - Pick-off terminal block

3047112

<https://www.phoenixcontact.com/us/products/3047112>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pick-off terminal block, nom. voltage: 1000 V, nominal current: 32 A, number of connections: 1, connection method: Screw connection, cross section: 0.14 mm² - 6 mm², mounting type: on base element, color: gray

Your advantages

- The fully insulated, optionally used pick-off terminal block enables voltage pick-off
- Large-surface marking
- Pick-off terminal block, for snapping into the side insertion funnel

Commercial data

Item number	3047112
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE19
Product key	BE1ZWX
GTIN	4017918975708
Weight per piece (including packing)	5.68 g
Weight per piece (excluding packing)	5.4 g
Customs tariff number	85369010
Country of origin	PL

AGK 4-UT 10 - Pick-off terminal block



3047112

<https://www.phoenixcontact.com/us/products/3047112>

Technical data

Notes

General

Note	The max. load current must not be exceeded by the total current of all connected conductors.
------	--

Product properties

Product type	Pick-off terminal
Product family	UT
Number of connections	1
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.02 W

Connection data

Number of connections per level	1
Nominal cross section	4 mm ²
Rated cross section AWG	10
Connection method	Screw connection
Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm
Stripping length	9 mm
Internal cylindrical gage	A4
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.14 mm ² ... 6 mm ²
Cross section AWG	26 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.14 mm ² ... 4 mm ²
Conductor cross-section, flexible [AWG]	26 ... 12 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 4 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 4 mm ²
2 conductors with same cross section, rigid	0.14 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible	0.14 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm ² ... 1.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1 mm ²
Nominal current	32 A (with 4 mm ² conductor cross-section)

AGK 4-UT 10 - Pick-off terminal block



3047112

<https://www.phoenixcontact.com/us/products/3047112>

Maximum load current	41 A (with 6 mm ² conductor cross-section)
Nominal voltage	1000 V

Ex data

Rated data (ATEX/IECEX)

Identification	⊕ II 2 GD Ex eb IIC Gb
Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	1204517 SZF 1-0,6X3,5
Ex temperature increase	40 K (34 A /4 mm ²)
Rated insulation voltage	400 V
output	(Permanent)

Ex level General

Rated voltage	440 V
Rated current	32 A
Maximum load current	41 A
Contact resistance	0.42 mΩ

Ex connection data General

Torque range	0.6 Nm ... 0.8 Nm
Nominal cross section	4 mm ²
Rated cross section AWG	12
Connection capacity rigid	0.14 mm ² ... 6 mm ²
Connection capacity AWG	26 ... 10
Connection capacity flexible	0.14 mm ² ... 4 mm ²
Connection capacity AWG	26 ... 12
2 conductors with same cross section, solid	0.14 mm ² ... 1.5 mm ²
2 conductors with the same cross-section AWG rigid	26 ... 16
2 conductors with same cross section, stranded	0.14 mm ² ... 1.5 mm ²
2 conductors with the same cross-section AWG flexible	26 ... 16

Dimensions

Width	8.1 mm
Height	36.3 mm
Depth	24.7 mm
Depth on NS 35/7,5	50.3 mm
Depth on NS 35/15	57.8 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C

AGK 4-UT 10 - Pick-off terminal block



3047112

<https://www.phoenixcontact.com/us/products/3047112>

Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	on base element
---------------	-----------------

AGK 4-UT 10 - Pick-off terminal block




3047112

<https://www.phoenixcontact.com/us/products/3047112>

Drawings

Circuit diagram



AGK 4-UT 10 - Pick-off terminal block



3047112

<https://www.phoenixcontact.com/us/products/3047112>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3047112>



cULus Recognized
Approval ID: E60425



cULus Recognized
Approval ID: E60425



ATEX
Approval ID: KEMA04ATEX2048U

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Only flexible conductors	440 V	32 A	-	0.14 - 4
Only rigid conductors	440 V	41 A	-	0.14 - 6



cUL Recognized
Approval ID: E192998

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	600 V	30 A	26 - 10	26 - 10
C				
	600 V	30 A	26 - 10	26 - 10



EAC Ex
Approval ID: RU C-DE.Ax07.B.03227



IECEx
Approval ID: IECEx KEM 06.0027U

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
Only flexible conductors	440 V	32 A	-	0.14 - 4
Only rigid conductors	440 V	41 A	-	0.14 - 6



UL Recognized
Approval ID: E192998

AGK 4-UT 10 - Pick-off terminal block



3047112

<https://www.phoenixcontact.com/us/products/3047112>

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B	600 V	30 A	26 - 10	-
C	600 V	30 A	26 - 10	-



CCC

Approval ID: 2020322313000622



UKCA-EX

Approval ID: DEKRA 21UKEX0304U



EAC Ex

Approval ID: KZ 7500525010101950

AGK 4-UT 10 - Pick-off terminal block



3047112

<https://www.phoenixcontact.com/us/products/3047112>

Classifications

ECLASS

ECLASS-13.0	27250308
ECLASS-15.0	27250308

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AGK 4-UT 10 - Pick-off terminal block



3047112

<https://www.phoenixcontact.com/us/products/3047112>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	23bc8778-9ff0-43f7-87b6-b17a9cf4699b

EF3.1 Climate Change

CO2e kg	0.013 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com