

# P-CO XL-UT - Component connector



3036799

<https://www.phoenixcontact.com/us/products/3036799>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component connector, for installing components that can be individually selected up to a diameter of 10 mm and power dissipation of up to 1 W, nom. voltage: 400 V, nominal current: 10 A, connection method: Plug-in connection, depth: 37.5 mm, width: 12.3 mm, height: 41.2 mm, number of positions: 1, color: gray, mounting type: Pluggable (slot)

## Your advantages

- Suitable for discreet components with high power dissipation
- Solderless spring-cage connection
- Can be used in all terminal blocks with disconnect zone

## Commercial data

Item number	3036799
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4055626369808
Weight per piece (including packing)	7.73 g
Weight per piece (excluding packing)	7.6 g
Customs tariff number	85366990
Country of origin	PL

# P-CO XL-UT - Component connector



3036799

<https://www.phoenixcontact.com/us/products/3036799>

## Technical data

### Notes

Notes on operation	Components with a wire diameter from 0.3 mm up to 1.2 mm can be used
--------------------	--


### Product properties

Product type	Component plug terminal block
Number of positions	1
Potentials	1

### Connection data

Connection method	Plug-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.08 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section flexible	0.08 mm <sup>2</sup> ... 1 mm <sup>2</sup>
Nominal cross section	1 mm <sup>2</sup>
Nominal current	10 A (the current is determined by the component used)
Maximum load current	10 A
Nominal voltage	400 V (the voltage is determined by the component used)

### Dimensions

Dimensional drawing	
Width	12.3 mm
Height	41.2 mm
Depth	37.5 mm

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed

# P-CO XL-UT - Component connector



3036799

<https://www.phoenixcontact.com/us/products/3036799>

Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

## Environmental and real-life conditions

### Ambient conditions


Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

## Mounting

Mounting type	Pluggable (slot)
---------------	------------------

Drawings

Dimensional drawing



# P-CO XL-UT - Component connector





3036799

<https://www.phoenixcontact.com/us/products/3036799>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3036799>

 <b>CSA</b> Approval ID: 13631				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
B	300 V	7 A	28 - 18	-
C	300 V	7 A	28 - 18	-

 <b>cULus Recognized</b> Approval ID: E60425				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
B	300 V	7 A	28 - 18	-
C	300 V	7 A	28 - 18	-

<b>DNV</b> Approval ID: TAE000010T				
---------------------------------------	--	--	--	--

# P-CO XL-UT - Component connector



3036799

<https://www.phoenixcontact.com/us/products/3036799>

## Classifications

### ECLASS

ECLASS-13.0	27250305
ECLASS-15.0	27250305

### ETIM

ETIM 10.0	EC002018
-----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# P-CO XL-UT - Component connector



3036799

<https://www.phoenixcontact.com/us/products/3036799>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.181 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)