

WS UT 35 - Warning label

3047387

<https://www.phoenixcontact.com/us/products/3047387>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning sign for UT terminal blocks



Your advantages

- Accidental actuation of the terminal points is prevented
- Warning labels and warning covers serve to cover and identify mains terminal blocks
- The warning labels snap into the screw and actuation shafts of the relevant terminal block
- Can be isolated lengthwise and crosswise

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3047387 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG20 |
| Product key | BG2511 |
| GTIN | 4046356074476 |
| Weight per piece (including packing) | 5.45 g |
| Weight per piece (excluding packing) | 4.99 g |
| Customs tariff number | 49119900 |
| Country of origin | PL |

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | Plant marker |
| Type | Rectangle |

Marking

| | |
|-----------------------------|-----------------|
| Number of individual labels | 1 |
| Printing | Lightning flash |

Dimensions

| | |
|--------|----------|
| Width | 16.00 mm |
| Height | 42.00 mm |
| Depth | 5.50 mm |

Material specifications

| | |
|---|--------------------------------|
| Color | multicolored (RAL -) |
| | yellow (RAL 1018) |
| | black (RAL 9005) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |
| Base element material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -60 °C ... 130 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |

Wipe resistance of inscriptions

WS UT 35 - Warning label



3047387

<https://www.phoenixcontact.com/us/products/3047387>

| | |
|---------------|-------------------------------------|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
|---------------|-------------------------------------|

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|---------|
| Mounting type | plug in |
|---------------|---------|

WS UT 35 - Warning label

3047387

<https://www.phoenixcontact.com/us/products/3047387>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281107 |
| ECLASS-15.0 | 27281107 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001777 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 55121700 |
|-------------|----------|

WS UT 35 - Warning label



3047387

<https://www.phoenixcontact.com/us/products/3047387>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com