


# USLKG 95 B - Protective conductor terminal block



3048195

<https://www.phoenixcontact.com/us/products/3048195>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective conductor terminal block, Screws with hexagonal socket, with opening for bridging, without mounting screw, number of connections: 2, number of positions: 1, connection method: Screw connection, Rated cross section: 95 mm<sup>2</sup>, cross section: 25 mm<sup>2</sup> - 95 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, NS 32, color: green-yellow

## Your advantages

- Reliable cable connection is ensured by three-point centering of the conductor in the prismatic sleeve base
- Screw locking by means of spring-loaded elements in the clamping part
- Low contact resistance of the contact surface due to ribbing

## Commercial data

Item number	3048195
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE12
Product key	BE1221
GTIN	4017918939441
Weight per piece (including packing)	309.76 g
Weight per piece (excluding packing)	309.76 g
Customs tariff number	85369010
Country of origin	PL

# USLKG 95 B - Protective conductor terminal block



3048195

<https://www.phoenixcontact.com/us/products/3048195>

## Technical data

### Notes

General	Screws with hexagonal socket
---------	------------------------------

### Product properties

Product type	Ground terminal block
Product family	USLKG
Number of positions	1
Number of connections	2
Number of rows	1

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	7.54 W

### Connection data

Grounding foot	Yes
Number of connections per level	2
Nominal cross section	95 mm <sup>2</sup>

### Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M8
Note	Please observe the current carrying capacity of the DIN rails.
Tightening torque	15 ... 20 Nm
Stripping length	30 mm
Connection in acc. with standard	IEC 60947-7-2
Conductor cross-section rigid	25 mm <sup>2</sup> ... 95 mm <sup>2</sup>
Cross section AWG	2 ... 3/0 (converted acc. to IEC)
Conductor cross-section flexible	25 mm <sup>2</sup> ... 95 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	2 ... 3/0 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	35 mm <sup>2</sup> ... 95 mm <sup>2</sup>
Flexible conductor cross-section (ferrule with plastic sleeve)	35 mm <sup>2</sup> ... 95 mm <sup>2</sup>
Nominal cross section	95 mm <sup>2</sup>

### Dimensions

Width	25 mm
Height	83 mm
Depth on NS 32	95.3 mm
Depth on NS 35/7,5	90.3 mm

# USLKG 95 B - Protective conductor terminal block



3048195

<https://www.phoenixcontact.com/us/products/3048195>

Depth on NS 35/15	97.8 mm
-------------------	---------

## Material specifications

Color	green-yellow
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA

## Mechanical properties

### Mechanical data

Open side panel	No
-----------------	----

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

## Standards and regulations

Connection in acc. with standard	IEC 60947-7-2
----------------------------------	---------------

## Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

# USLKG 95 B - Protective conductor terminal block



3048195

<https://www.phoenixcontact.com/us/products/3048195>

## Drawings

Circuit diagram



# USLKG 95 B - Protective conductor terminal block



3048195

<https://www.phoenixcontact.com/us/products/3048195>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3048195>



**EAC**

Approval ID: KZ7500651131219505

# USLKG 95 B - Protective conductor terminal block



3048195

<https://www.phoenixcontact.com/us/products/3048195>

## Classifications

### ECLASS

ECLASS-13.0	27250103
ECLASS-15.0	27250103

### ETIM

ETIM 10.0	EC000901
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# USLKG 95 B - Protective conductor terminal block



3048195

<https://www.phoenixcontact.com/us/products/3048195>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)