

# USED 27 N - Fuse modular terminal block



3048373

<https://www.phoenixcontact.com/us/products/3048373>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse modular terminal block, fuse type: Screw cartridge, fuse type: D II / E 27, nom. voltage: 500 V, nominal current: 25 A, connection method: Screw connection, Rated cross section: 35 mm<sup>2</sup>, cross section: 1.5 mm<sup>2</sup>- 35 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: light gray

## Your advantages

- Original DIAZED®-E 27 threads are used in closed housing
- The major advantage of the DIAZED® system is its dielectric strength of up to 500 V
- Conductor cross-sections of up to 35 mm<sup>2</sup> can be connected with the user-friendly spring-cage connection
- This fuse terminal block accommodates DIAZED® fuses

## Commercial data

Item number	3048373
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BE12
Product key	BE1235
GTIN	4017918976286
Weight per piece (including packing)	143 g
Weight per piece (excluding packing)	139.05 g
Customs tariff number	85363030
Country of origin	DE

# USED 27 N - Fuse modular terminal block



3048373

<https://www.phoenixcontact.com/us/products/3048373>

## Technical data

### Notes

Order information:	Fuse-link not supplied as standard
Note on application	for NEOZED fuse-links

### Product properties

Product type	Fuse terminal block
Pitch	40 mm
Number of connections	2
Number of rows	1
Potentials	1

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Fuse type	Screw cartridge
Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	4.06 W
Fuse	D II / E 27

### Connection data

Number of connections per level	2
Nominal cross section	35 mm <sup>2</sup>

### Level 1

Connection method	Screw connection
Screw thread	M6
Tightening torque	3.5 ... 4 Nm
Stripping length	19 mm
Internal cylindrical gage	B8
Conductor cross-section rigid	1.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>
Cross section AWG	14 ... 2 (converted acc. to IEC)
Conductor cross-section flexible	1.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>
Conductor cross-section, flexible [AWG]	14 ... 2 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>
Flexible conductor cross-section (ferrule with plastic sleeve)	1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>
Cross-section with insertion bridge, rigid	25 mm <sup>2</sup>
Cross-section with insertion bridge, flexible	25 mm <sup>2</sup>
2 conductors with same cross section, rigid	1.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>
2 conductors with same cross section, flexible	1.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	1.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>

# USED 27 N - Fuse modular terminal block



3048373

<https://www.phoenixcontact.com/us/products/3048373>

2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Nominal cross section	35 mm <sup>2</sup>
Nominal current	25 A (the current is determined by the fuse used)
Maximum load current	25 A (with 35 mm <sup>2</sup> conductor cross-section)
Nominal voltage	500 V (the voltage is determined by the fuse used)

## Dimensions

Width	40 mm
Height	80 mm
Depth on NS 35/7,5	62.5 mm
Depth on NS 35/15	70 mm
Pitch	40 mm

## Material specifications

Color	beige (RAL 7032)
Flammability rating according to UL 94	V2
Insulating material group	IIIb
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

## Mechanical properties

### Mechanical data

Open side panel	No
-----------------	----

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

## Mounting

Mounting type	NS 35/7,5
	NS 35/15

# USED 27 N - Fuse modular terminal block

3048373

<https://www.phoenixcontact.com/us/products/3048373>



## Drawings

Circuit diagram



# USED 27 N - Fuse modular terminal block



3048373

<https://www.phoenixcontact.com/us/products/3048373>

## Classifications

### ECLASS

ECLASS-13.0	27250113
ECLASS-15.0	27250113

### ETIM

ETIM 10.0	EC000899
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# USED 27 N - Fuse modular terminal block



3048373

<https://www.phoenixcontact.com/us/products/3048373>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.78 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)