

UK 3-MVSTB-5,08-2DIO 3POL - Feed-through terminal block



3048784

<https://www.phoenixcontact.com/us/products/3048784>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, with integrated diode, nom. voltage: 250 V, nominal current: 12 A, number of connections: 6, number of positions: 3, connection method: Screw/plug-in connection, 1st level connection left, cross section: 0.2 mm² - 4 mm², mounting type: NS 32, NS 35/15, NS 35/7,5, color: gray

Commercial data

Item number	3048784
Packing unit	50 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BE1241
GTIN	4046356284332
Weight per piece (including packing)	21.464 g
Weight per piece (excluding packing)	21.464 g
Country of origin	PL

UK 3-MVSTB-5,08-2DIO 3POL - Feed-through terminal block



3048784

<https://www.phoenixcontact.com/us/products/3048784>

Technical data

Product properties

Product type	Plug-in terminal block
Number of positions	3
Pitch	5.08 mm
Number of connections	6
Number of rows	1
Potentials	3

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	4 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

1st level connection left

Connection method	Screw/plug-in connection
Screw thread	M3
Tightening torque	0.5 ... 0.6 Nm
Stripping length	8 mm
Internal cylindrical gage	A3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Cross section AWG	24 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	24 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.25 mm ² ... 2.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 1.5 mm ²
2 conductors with same cross section, rigid	0.2 mm ² ... 1.5 mm ²
2 conductors with same cross section, flexible	0.2 mm ² ... 1 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.25 mm ² ... 0.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1 mm ²
Nominal current	12 A
Maximum load current	12 A (with 4 mm ² conductor cross-section)
Nominal voltage	250 V

Dimensions

Width	15.3 mm
End cover width	2.5 mm

UK 3-MVSTB-5,08-2DIO 3POL - Feed-through terminal block



3048784

<https://www.phoenixcontact.com/us/products/3048784>

Pitch	5.08 mm
-------	---------

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 32
	NS 35/15
	NS 35/7,5

UK 3-MVSTB-5,08-2DIO 3POL - Feed-through terminal block



3048784

<https://www.phoenixcontact.com/us/products/3048784>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UK 3-MVSTB-5,08-2DIO 3POL - Feed-through terminal block



3048784

<https://www.phoenixcontact.com/us/products/3048784>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ac9127b5-9340-4860-8e3c-32a57f111614

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com