


QTCU 2,5-TWIN-PE - Protective conductor terminal block

3050329

<https://www.phoenixcontact.com/us/products/3050329>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective conductor terminal block, connection method: Quick connection, cross section: 0.5 mm² - 2.5 mm², connection method: Screw connection, cross section: 0.14 mm² - 6 mm², mounting: NS 35/7,5, NS 35/15, color: green-yellow

Your advantages

- Same shape and pitch as the feed-through terminal blocks
- Contact is made free from mechanical and electrical errors by simply snapping onto the DIN rail
- All the requirements of standard IEC 60947-7-2 are met

Commercial data

Item number	3050329
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE03
Product key	BE3129
GTIN	4046356056168
Weight per piece (including packing)	18.241 g
Weight per piece (excluding packing)	18.24 g
Customs tariff number	85369010
Country of origin	CN

QTCU 2,5-TWIN-PE - Protective conductor terminal block



3050329

<https://www.phoenixcontact.com/us/products/3050329>

Technical data

Product properties

Product type	Ground terminal block
Number of connections	3
Number of rows	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

Grounding foot	Yes
Number of connections per level	3
Frequency of connections with the same cross section	100
Nominal cross section	2.5 mm ²
Connection method	Quick connection
Note	Please observe the current carrying capacity of the DIN rails.
Material wire insulation	PVC / PE
Connection in acc. with standard	IEC 60947-7-2
Conductor cross-section rigid	0.5 mm ² ... 2.5 mm ²
Cross section AWG	20 ... 14 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	20 ... 14 (converted acc. to IEC)
Connection method	Screw connection
Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm
Stripping length	9 mm
Connection in acc. with standard	IEC 60947-7-2
Conductor cross-section rigid	0.14 mm ² ... 6 mm ²
Cross section AWG	26 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.14 mm ² ... 4 mm ²
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm ² ... 4 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.14 mm ² ... 4 mm ²

Ex data

Rated data (ATEX/IECEx)

Identification	⊕ II 2 GD Ex eb IIC Gb
Operating temperature range	-45 °C ... 90 °C

QTCU 2,5-TWIN-PE - Protective conductor terminal block



3050329

<https://www.phoenixcontact.com/us/products/3050329>

Ex-certified accessories	3050510 D-QTCU 2,5 TWIN
	1204517 SZF 1-0,6X3,5
	3022276 CLIPFIX 35-5
	3022218 CLIPFIX 35
output	(Permanent)

Ex connection data Fast connection

Nominal cross section	2.5 mm ²
Rated cross section AWG	14
Connection capacity rigid	0.5 mm ² ... 2.5 mm ²
Connection capacity AWG	20 ... 14
Connection capacity flexible	0.5 mm ² ... 2.5 mm ²
Connection capacity AWG	20 ... 14
Frequency of connections with the same cross section	100

Ex connection data Screw connection

Torque range	0.6 Nm ... 0.8 Nm
Nominal cross section	2.5 mm ²
Rated cross section AWG	14
Connection capacity rigid	0.14 mm ² ... 6 mm ²
Connection capacity AWG	26 ... 10
Connection capacity flexible	0.14 mm ² ... 4 mm ²
Connection capacity AWG	26 ... 12

Dimensions

Width	6.2 mm
End cover width	2.2 mm
Height	82.5 mm
Depth on NS 35/7,5	42.8 mm
Depth on NS 35/15	50.3 mm

Material specifications

Color	green-yellow
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

QTCU 2,5-TWIN-PE - Protective conductor terminal block



3050329

<https://www.phoenixcontact.com/us/products/3050329>

Cable/line

Wire diameter incl. insulation	3.8 mm
--------------------------------	--------

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-2
	IEC 60947-7-2

Mounting

Mounting type	NS 35/7,5
	NS 35/15

QTCU 2,5-TWIN-PE - Protective conductor terminal block



3050329

<https://www.phoenixcontact.com/us/products/3050329>

Drawings

Circuit diagram



QTCU 2,5-TWIN-PE - Protective conductor terminal block




3050329

<https://www.phoenixcontact.com/us/products/3050329>


Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3050329>


 cULus Recognized Approval ID: E60425		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B					
Screw connection	-	-	26 - 10	-	
Fast connection	-	-	20 - 14	-	
C					
Screw connection	-	-	26 - 10	-	
Fast connection	-	-	20 - 14	-	

 ClassNK NK Approval ID: 09 ME 139	
--	--

ABS Approval ID: 22-2196825-PDA	
---	--

 IECEX Approval ID: IECEXKIWA19.0011U	
--	--

 ATEX Approval ID: KIWA19ATEX0019U	
---	--

 CCC Approval ID: 2020322313000625	
---	--

 UKCA-EX Approval ID: CSAE 22UKEX1429U	
---	--

 EAC Ex Approval ID: KZ 7500525010101950	
---	--

QTCU 2,5-TWIN-PE - Protective conductor terminal block



3050329

<https://www.phoenixcontact.com/us/products/3050329>

Classifications

ECLASS

ECLASS-13.0

27250202

ETIM

ETIM 9.0

EC000901

UNSPSC

UNSPSC 21.0

39121400

QTCU 2,5-TWIN-PE - Protective conductor terminal block



3050329

<https://www.phoenixcontact.com/us/products/3050329>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f2fd2358-b89e-4b90-97f4-f4a6a5bd6dff

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com