


UTT 4-PV BU - Feed-through terminal block



3059265

<https://www.phoenixcontact.com/us/products/3059265>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, with equipotential bonder, nom. voltage: 800 V, nominal current: 30 A, connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.14 mm² - 6 mm², mounting type: NS 35/7,5, NS 35/15, color: blue

Your advantages

- Globally recognized: Internationally proven screw connection
- Maintenance-free and vibration-resistant thanks to the patented Reakdyn principle
- Space savings and flexibility with the connection of two identical conductors
- Long-term stable connections with the use of high-quality materials
- Low self-heating due to high contact forces
- Maximum efficiency in the smallest space - thanks to integrated level bridging, the connections are connected across levels
- High space savings thanks to the compact integration of two separate circuits in a single terminal block

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3059265 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE01 |
| Product key | BE1114 |
| GTIN | 4046356495943 |
| Weight per piece (including packing) | 19.946 g |
| Weight per piece (excluding packing) | 19.946 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

UTT 4-PV BU - Feed-through terminal block



3059265

<https://www.phoenixcontact.com/us/products/3059265>

Technical data

Product properties

| | |
|-----------------------|----------------------------|
| Product type | Multi-level terminal block |
| Product family | UT |
| Number of connections | 4 |
| Number of rows | 2 |
| Potentials | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 8 kV |
| Maximum power dissipation for nominal condition | 1.02 W |

Connection data

| | |
|---------------------------------|-------------------|
| Number of connections per level | 2 |
| Nominal cross section | 4 mm ² |

Level 1+2

| | |
|---|---|
| Connection method | Screw connection |
| Screw thread | M3 |
| Tightening torque | 0.6 ... 0.8 Nm |
| Stripping length | 9 mm |
| Internal cylindrical gage | A4 |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross-section rigid | 0.14 mm ² ... 6 mm ² |
| Cross section AWG | 26 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.14 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] | 26 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 4 mm ² |
| 2 conductors with same cross section, rigid | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with same cross section, flexible | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² ... 2.5 mm ² |
| Nominal cross section | 4 mm ² |
| Nominal current | 30 A |
| Maximum load current | 36 A (with 6 mm ² conductor cross-section) |
| Nominal voltage | 800 V |

UTT 4-PV BU - Feed-through terminal block



3059265

<https://www.phoenixcontact.com/us/products/3059265>

Ex data

Rated data (ATEX/IECEX)

| | |
|--|-------------------------------------|
| Identification | ⊕ II 2 GD Ex eb IIC Gb |
| Operating temperature range | -60 °C ... 110 °C |
| Ex-certified accessories | 3047293 D-UTT 2,5/4 |
| | 3047303 DP-UTT 2,5/4 |
| | 3047316 ATP-UTT 2,5/4 |
| | 1212587 SF-SL 0,6X3,5-100 S-VDE |
| | 3022276 CLIPFIX 35-5 |
| | 3022218 CLIPFIX 35 |
| List of bridges | Plug-in bridge / FBS 2-6 / 3030336 |
| | Plug-in bridge / FBS 3-6 / 3030242 |
| | Plug-in bridge / FBS 4-6 / 3030255 |
| | Plug-in bridge / FBS 5-6 / 3030349 |
| | Plug-in bridge / FBS 10-6 / 3030271 |
| | Plug-in bridge / FBS 20-6 / 3030365 |
| Bridge data | 25.5 A / 4 mm ² |
| Ex temperature increase | 40 K (32.8 A / 4 mm ²) |
| for bridging with bridge | 440 V |
| - At bridging between non-adjacent terminal blocks | 275 V |
| - At bridging between non-adjacent terminal blocks via PE terminal block | 275 V |
| - At cut-to-length bridging with cover | 220 V |
| - At cut-to-length bridging with partition plate | 176 V |
| Rated insulation voltage | 400 V |
| output | (Permanent) |

Ex level General

| | |
|----------------------|--------|
| Rated voltage | 440 V |
| Rated current | 29.5 A |
| Maximum load current | 33.5 A |

Ex connection data General

| | |
|---|--|
| Torque range | 0.6 Nm ... 0.8 Nm |
| Nominal cross section | 4 mm ² |
| Rated cross section AWG | 12 |
| Connection capacity rigid | 0.14 mm ² ... 6 mm ² |
| Connection capacity AWG | 26 ... 10 |
| Connection capacity flexible | 0.14 mm ² ... 4 mm ² |
| Connection capacity AWG | 26 ... 12 |
| 2 conductors with same cross section, solid | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross-section AWG rigid | 26 ... 16 |
| 2 conductors with same cross section, stranded | 0.14 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross-section AWG flexible | 26 ... 16 |

UTT 4-PV BU - Feed-through terminal block



3059265

<https://www.phoenixcontact.com/us/products/3059265>

| | |
|------------------------|-------------|
| output | (Permanent) |
| Ex level Level 1 | |
| Contact resistance | 0.35 mΩ |
| output | (Permanent) |
| Ex level Level 2 | |
| Contact resistance | 0.2 mΩ |
| output | (Permanent) |
| Ex level PV connection | |
| Contact resistance | 0.5 mΩ |

Dimensions

| | |
|--------------------|---------|
| Width | 6.2 mm |
| End cover width | 2.2 mm |
| Height | 69.9 mm |
| Depth on NS 35/7,5 | 65 mm |
| Depth on NS 35/15 | 72.5 mm |

Material specifications

| | |
|---|-----------------|
| Color | blue (RAL 5015) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

Mechanical data

| | |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; |
|---------------------------------|--|

UTT 4-PV BU - Feed-through terminal block



3059265

<https://www.phoenixcontact.com/us/products/3059265>

| | |
|--|---|
| | for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

UTT 4-PV BU - Feed-through terminal block


3059265

<https://www.phoenixcontact.com/us/products/3059265>



Drawings

Circuit diagram



UTT 4-PV BU - Feed-through terminal block



3059265

<https://www.phoenixcontact.com/us/products/3059265>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3059265>

| |
|---------------------------------------|
| DNV Approval ID: TAE00001S9 |
|---------------------------------------|

| | | | | |
|----------------------------------|-----------------------|-----------------------|-------------------|----------------------|
| CSA Approval ID: 13631 | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 300 V | 30 A | 26 - 10 | - |
| C | 300 V | 30 A | 26 - 10 | - |
| D | 600 V | 5 A | 26 - 10 | - |

| | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| cULus Recognized Approval ID: E60425 | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 300 V | 30 A | 26 - 10 | - |
| Multi-conductor connection | 300 V | 30 A | 26 - 14 | - |
| C | 300 V | 30 A | 26 - 10 | - |
| Multi-conductor connection | 300 V | 30 A | 26 - 14 | - |
| D | 600 V | 5 A | 26 - 10 | - |
| Multi-conductor connection | 600 V | 5 A | 26 - 14 | - |

| |
|---|
| ATEX Approval ID: KEMA06ATEX0017U |
|---|

| | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| cUL Recognized Approval ID: E192998 | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 300 V | 30 A | 26 - 10 | - |
| C | 300 V | 30 A | 26 - 10 | - |

UTT 4-PV BU - Feed-through terminal block



3059265

<https://www.phoenixcontact.com/us/products/3059265>



IECEX

Approval ID: IECEX KEM 06.0013U



UL Recognized

Approval ID: E192998

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B | | | | |
| | 300 V | 30 A | 26 - 10 | - |
| C | | | | |
| | 300 V | 30 A | 26 - 10 | - |



CCC

Approval ID: 2020322313000622



UKCA-EX

Approval ID: DEKRA 21UKEX0305U



EAC Ex

Approval ID: KZ 7500525010101950

UTTB 4-PV BU - Feed-through terminal block



3059265

<https://www.phoenixcontact.com/us/products/3059265>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250102 |
| ECLASS-15.0 | 27250102 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UTTB 4-PV BU - Feed-through terminal block



3059265

<https://www.phoenixcontact.com/us/products/3059265>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 2987a391-0187-4de4-b3bf-46297a609c68 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.024 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com