

# SP 4/10 - Plug

3042984

<https://www.phoenixcontact.com/us/products/3042984>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug, nom. voltage: 800 V, nominal current: 32 A, number of positions: 10, connection method: Spring-cage connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.08 mm<sup>2</sup>- 6 mm<sup>2</sup>, color: gray

## Your advantages

- Large-surface labeling option
- Practical coding option
- Tested for railway applications

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3042984       |
| Packing unit                         | 25 pc         |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BE02          |
| Product key                          | BE2144        |
| GTIN                                 | 4017918956318 |
| Weight per piece (including packing) | 42.96 g       |
| Weight per piece (excluding packing) | 42.96 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

# SP 4/10 - Plug

3042984

<https://www.phoenixcontact.com/us/products/3042984>



## Technical data

### Notes

|                    |   |
|--------------------|---|
| Notes on operation | COMBI connectors are connectors without switching power in accordance with IEC 61984 and can be connected or disconnected without load or voltage when used as intended |
|--------------------|---|

### General

|      |   |
|------|---|
| Note | With a free-hanging connection, an insulating foil has to be placed between the plug connection and electrically conductive surfaces. |
|------|---|

### Product properties

|                     |               |
|---------------------|---------------|
| Product type        | Terminal plug |
| Number of positions | 10            |
| Pitch               | 6.2 mm        |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                     |      |
|---------------------|------|
| Rated surge voltage | 8 kV |
|---------------------|------|

### Connection data

|   |   |
|---|---|
| Nominal cross section   | 4 mm <sup>2</sup>                                     |
| Connection method   | Spring-cage connection                                |
| Stripping length  | 8 mm ... 10 mm  |
| Internal cylindrical gage   | A4  |
| Connection in acc. with standard  | IEC 61984   |
| Conductor cross-section rigid   | 0.08 mm <sup>2</sup> ... 6 mm <sup>2</sup>            |
| Cross section AWG   | 28 ... 10 (converted acc. to IEC)                     |
| Conductor cross-section flexible  | 0.08 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| Conductor cross-section, flexible [AWG]   | 28 ... 12 (converted acc. to IEC)                     |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup>             |
| Nominal cross section   | 4 mm <sup>2</sup>                                     |
| Nominal current   | 32 A  |
| Maximum load current  | 32 A (with 6 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage   | 800 V   |

### Dimensions

|        |       |
|--------|-------|
| Width  | 62 mm |
| Height | 21 mm |

# SP 4/10 - Plug



3042984

<https://www.phoenixcontact.com/us/products/3042984>

|        |         |
|--------|---------|
| Depth  | 41.5 mm |
| Length | 21 mm   |
| Pitch  | 6.2 mm  |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group   | I               |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Electrical tests

### Surge voltage test

|  |             |
|--|-------------|
| Result   | Test passed |
| Short-time withstand current 4 mm <sup>2</sup> | 0.48 kA     |
| Result   | Test passed |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 2 kV        |
| Result                | Test passed |

## Mechanical tests

### Attachment on the carrier

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

## Environmental and real-life conditions

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|               |  |
|---------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2018-05              |
| Spectrum      | Long life test category 1, class B, body mounted |

# SP 4/10 - Plug



3042984

<https://www.phoenixcontact.com/us/products/3042984>

|                        |  |
|------------------------|--|
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$ |
| ASD level              | $0.964 \text{ (m/s}^2\text{)}^2\text{/Hz}$     |
| Acceleration           | 0.58g  |
| Test duration per axis | 5 h  |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

## Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 5g                                |
| Shock duration                 | 30 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |
| Result                         | Test passed                       |

## Ambient conditions

|  |   |
|--|---|
| Ambient temperature (operation)          | -60 °C (max. operating temperature see derating curve)                    |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C   |
| Permissible humidity (operation)         | 20 % ... 90 %   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

## Standards and regulations

|                                  |           |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|


# SP 4/10 - Plug

3042984

<https://www.phoenixcontact.com/us/products/3042984>




## Drawings




Derating curve for spring-cage terminals ST 4/1P.. and ST 4/2P.. with all plug versions SP 4/... . The derating curves are determined by multiplying the values of the base curves by the factor 0.8.


Diagram



Derating curve for the spring-cage terminal with all plug versions SP 4/... .



Derating curve for ST 4/ 1P and for all plug versions SP...



The figure shows the derating curve of the ST 4... terminal block in connection with the SP 4 plug

# SP 4/10 - Plug

3042984

<https://www.phoenixcontact.com/us/products/3042984>



Circuit diagram



# SP 4/10 - Plug




3042984


<https://www.phoenixcontact.com/us/products/3042984>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3042984>

|  <b>CSA</b><br>Approval ID: 13631 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B  | 600 V                 | 30 A                  | 24 - 12           | -                           |
| C  | 600 V                 | 30 A                  | 24 - 12           | -                           |

|  <b>IECEE CB Scheme</b><br>Approval ID: DE1-62736/B1/B2 |  |  |  |  |
|--|--|--|--|--|
|--|--|--|--|--|

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B  | 600 V                 | 30 A                  | 28 - 10           | -                           |
| C  | 600 V                 | 30 A                  | 28 - 10           | -                           |

|  <b>VDE Zeichengenehmigung</b><br>Approval ID: 40019518 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
| Only flexible conductors   | 800 V                 | -                     | -                 | 0.2 - 4                     |
| Only rigid conductors  | 800 V                 | -                     | -                 | 0.2 - 6                     |

|  <b>EAC</b><br>Approval ID: KZ7500651131219505 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

# SP 4/10 - Plug

3042984

<https://www.phoenixcontact.com/us/products/3042984>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250306 |
| ECLASS-15.0 | 27250306 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002021 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SP 4/10 - Plug



3042984

<https://www.phoenixcontact.com/us/products/3042984>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.297 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)