

SC 2,5/ 4 X83 - COMBI coupling

3061088

<https://www.phoenixcontact.com/us/products/3061088>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



COMBI coupling, nom. voltage: 500 V, nominal current: 24 A, number of connections: 1, number of positions: 4, connection method: Plug-in connection, Rated cross section: 2.5 mm², cross section: 0.08 mm² - 4 mm², color: gray

Your advantages

- Standard strain relief can be used

Commercial data

Item number	3061088
Packing unit	25 pc
Minimum order quantity	1 pc
Product key	BE2145
GTIN	4046356153157
Weight per piece (including packing)	15.97 g
Weight per piece (excluding packing)	15.97 g
Country of origin	PL

SC 2,5/ 4 X83 - COMBI coupling



3061088

<https://www.phoenixcontact.com/us/products/3061088>

Technical data

Product properties

Product type	Terminal coupling
Number of positions	4
Pitch	5.2 mm
Number of connections	1
Number of rows	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

Nominal cross section	2.5 mm ²
Connection method	Plug-in connection
Stripping length	10 mm
Internal cylindrical gage	A3
Connection in acc. with standard	IEC 61984
Conductor cross-section rigid	0.08 mm ² ... 4 mm ²
Cross section AWG	28 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.08 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	28 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm ² ... 2.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.14 mm ² ... 2.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ²
Nominal cross section	2.5 mm ²
Nominal current	24 A
Maximum load current	24 A (with 4 mm ² conductor cross-section)
Nominal voltage	500 V

Dimensions

Width	20.8 mm
End cover width	2.2 mm
Height	18.8 mm
Pitch	5.2 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

SC 2,5/ 4 X83 - COMBI coupling



3061088

<https://www.phoenixcontact.com/us/products/3061088>

Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 61984
----------------------------------	-----------

SC 2,5/ 4 X83 - COMBI coupling

3061088

<https://www.phoenixcontact.com/us/products/3061088>



Drawings

Circuit diagram



SC 2,5/ 4 X83 - COMBI coupling

3061088

<https://www.phoenixcontact.com/us/products/3061088>



Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SC 2,5/ 4 X83 - COMBI coupling



3061088

<https://www.phoenixcontact.com/us/products/3061088>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com