

# UT 4-TWIN-PE - Protective conductor terminal block



3044380

<https://www.phoenixcontact.com/us/products/3044380>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective conductor terminal block, number of connections: 3, connection method: Screw connection, 1 level, cross section:  $0.14 \text{ mm}^2 - 6 \text{ mm}^2$ , mounting type: NS 35/7,5, NS 35/15, color: green-yellow

## Your advantages

- Globally recognized: Internationally proven screw connection
- Maintenance-free and vibration-resistant thanks to the patented Reakdyn principle
- Meet the requirements of DIN EN 60947-7-2 or IEC 60947-7-2 for protective conductor connections
- High level of safety thanks to the low-resistance connection to the ground potential via the top-hat rail
- Direct contacting with the DIN rail enables fast, error-free grounding without additional wiring effort.
- Full flexibility thanks to the standardized CLIPLINE complete bridging, marking, and testing accessories

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3044380       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1122        |
| GTIN                                 | 4046356055383 |
| Weight per piece (including packing) | 17.432 g      |
| Weight per piece (excluding packing) | 16.98 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | DE            |

# UT 4-TWIN-PE - Protective conductor terminal block



3044380

<https://www.phoenixcontact.com/us/products/3044380>

## Technical data

### Notes

#### General

|      |  |
|------|--|
| Note | The max. load current must not be exceeded by the total current of all connected conductors. |
|------|--|

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | Ground terminal block |
| Product family        | UT                    |
| Area of application   | Railway industry      |
|                       | Machine building      |
|                       | Plant engineering     |
|                       | Process industry      |
| Number of connections | 3                     |
| Number of rows        | 1                     |

#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 1.02 W |

### Connection data

|                                 |                   |
|---------------------------------|-------------------|
| Grounding foot                  | Yes               |
| Number of connections per level | 3                 |
| Nominal cross section           | 4 mm <sup>2</sup> |

#### 1 level

|   |  |
|---|--|
| Connection method   | Screw connection   |
| Screw thread  | M3   |
| Note  | Please observe the current carrying capacity of the DIN rails. |
| Tightening torque   | 0.5 ... 0.8 Nm   |
| Stripping length  | 9 mm   |
| Internal cylindrical gage                                     | A4   |
| Connection in acc. with standard                              | IEC 60947-7-2  |
| Conductor cross-section rigid                                 | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>                     |
| Cross section AWG   | 26 ... 10 (converted acc. to IEC)                              |
| Conductor cross-section flexible                              | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>                     |
| Conductor cross-section, flexible [AWG]                       | 26 ... 10 (converted acc. to IEC)                              |
| Conductor cross-section flexible ultrasound-compressed        | 0.34 mm <sup>2</sup> ... 6 mm <sup>2</sup>                     |
| Conductor cross-section, flexible [AWG] ultrasound-compressed | 22 ... 10 (converted acc. to IEC)                              |

# UT 4-TWIN-PE - Protective conductor terminal block



3044380

<https://www.phoenixcontact.com/us/products/3044380>

|   |  |
|---|--|
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup> |

## Ex data

### Rated data (ATEX/IECEx)

|                             |                                 |
|-----------------------------|---------------------------------|
| Identification              | ⊕ II 2 GD Ex eb IIC Gb          |
| Operating temperature range | -60 °C ... 110 °C               |
| Ex-certified accessories    | 3047141 D-UT 2,5/4-TWIN         |
|                             | 3047109 DS-UT 2,5/4             |
|                             | 1212587 SF-SL 0,6X3,5-100 S-VDE |
|                             | 3022276 CLIPFIX 35-5            |
|                             | 3022218 CLIPFIX 35              |
| output                      | (Permanent)                     |

### Ex connection data General

|                              |  |
|------------------------------|--|
| Torque range                 | 0.6 Nm ... 0.8 Nm                          |
| Nominal cross section        | 4 mm <sup>2</sup>                          |
| Rated cross section AWG      | 12   |
| Connection capacity rigid    | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
| Connection capacity AWG      | 26 ... 10                                  |
| Connection capacity flexible | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup> |
| Connection capacity AWG      | 26 ... 12                                  |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 6.2 mm  |
| End cover width    | 2.2 mm  |
| Height             | 57.8 mm |
| Depth              | 46.9 mm |
| Depth on NS 35/7,5 | 47.5 mm |
| Depth on NS 35/15  | 55 mm   |

## Material specifications

|   |              |
|---|--------------|
| Color   | green-yellow |
| Flammability rating according to UL 94                                  | V0           |
| Insulating material group   | I            |
| Insulating material   | PA           |
| Static insulating material application in cold                          | -60 °C       |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C       |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C       |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3  |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3  |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3  |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3  |

# UT 4-TWIN-PE - Protective conductor terminal block



3044380

<https://www.phoenixcontact.com/us/products/3044380>

|   |          |
|---|----------|
| Calorimetric heat release NFPA 130 (ASTM E 1354)        | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162)              | passed   |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed   |
| Smoke gas toxicity NFPA 130 (SMP 800C)                  | passed   |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Oscillation/broadband noise

|                        |  |
|------------------------|--|
| Specification          | EN 50155:2021-07                               |
| Spectrum               | Long life test category 2, bogie-mounted       |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz      |
| Acceleration           | 3.12g  |
| Test duration per axis | 5 h  |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

### Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 30g                                 |
| Shock duration                 | 18 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-2 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# UT 4-TWIN-PE - Protective conductor terminal block




3044380

<https://www.phoenixcontact.com/us/products/3044380>

## Drawings

Circuit diagram



# UT 4-TWIN-PE - Protective conductor terminal block



3044380

<https://www.phoenixcontact.com/us/products/3044380>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3044380>

**DNV**  
Approval ID: TAE00001S9

**cUL Recognized**  
Approval ID: FILE E 60425

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|-------|-----------------------|-----------------------|-------------------|----------------------|
| keine | -                     | -                     | 26 - 10           | -                    |

**CB Scheme**  
Approval ID: De1-63049

**VDE approval of drawings**  
Approval ID: 40041280

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|-------|-----------------------|-----------------------|-------------------|----------------------|
| keine | -                     | -                     | -                 | 0.14 - 6             |

**ATEX**  
Approval ID: KEMA06ATEX0017U

**cUL Recognized**  
Approval ID: E192998

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|-----------------------|-----------------------|-------------------|----------------------|
| B | -                     | -                     | 26 - 10           | -                    |
| C | -                     | -                     | 26 - 10           | -                    |
| D | -                     | -                     | 26 - 10           | -                    |

**EAC Ex**  
Approval ID: KZ 7500525010101950

**IECEx**  
Approval ID: IECEx KEM 06.0013U

# UT 4-TWIN-PE - Protective conductor terminal block




3044380

<https://www.phoenixcontact.com/us/products/3044380>

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B | -                     | -                     | 26 - 10           | -                           |
| C | -                     | -                     | 26 - 10           | -                           |
| D | -                     | -                     | 26 - 10           | -                           |

 **CCC**  
Approval ID: 2020322313000622

 **UKCA-EX**  
Approval ID: DEKRA 21UKEX0305U

# UT 4-TWIN-PE - Protective conductor terminal block



3044380

<https://www.phoenixcontact.com/us/products/3044380>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250103 |
| ECLASS-15.0 | 27250103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000901 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UT 4-TWIN-PE - Protective conductor terminal block



3044380

<https://www.phoenixcontact.com/us/products/3044380>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | b7e4c2b3-0fe1-4f64-b215-84142b229a3c |

### EF3.1 Climate Change

|         |              |
|---------|--------------|
| CO2e kg | 0.03 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)