

# UPBV 4/ 1 GNYE - Plug



3045279

<https://www.phoenixcontact.com/us/products/3045279>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug, nom. voltage: 800 V, nominal current: 32 A, number of positions: 1, connection method: Screw connection, Rated cross section: 4 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup>- 6 mm<sup>2</sup>, color: green-yellow

## Your advantages

- Can be bridged with FBS ... standard bridges
- Connector with lateral conductor connection direction
- The connected conductors can be led directly into the cable duct to save space

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3045279       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1144        |
| GTIN                                 | 4046356113328 |
| Weight per piece (including packing) | 6.6 g         |
| Weight per piece (excluding packing) | 6.6 g         |
| Customs tariff number                | 85366990      |
| Country of origin                    | TR            |

# UPBV 4/ 1 GNYE - Plug



3045279

<https://www.phoenixcontact.com/us/products/3045279>

## Technical data

### Notes

|                    |   |
|--------------------|---|
| Notes on operation | COMBI connectors are connectors without switching power in accordance with IEC 61984 and can be connected or disconnected without load or voltage when used as intended |
|--------------------|---|

### Product properties

|                     |               |
|---------------------|---------------|
| Product type        | Terminal plug |
| Number of positions | 1             |
| Pitch               | 6.2 mm        |
| Potentials          | 1             |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|                     |      |
|---------------------|------|
| Rated surge voltage | 8 kV |
|---------------------|------|

### Connection data

|   |   |
|---|---|
| Nominal cross section   | 4 mm <sup>2</sup>                                     |
| Connection method   | Screw connection                                      |
| Screw thread  | M3  |
| Tightening torque   | 0.6 ... 0.8 Nm  |
| Stripping length  | 9 mm  |
| Internal cylindrical gage   | A4  |
| Connection in acc. with standard  | IEC 61984   |
| Conductor cross-section rigid   | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>            |
| Cross section AWG   | 26 ... 10 (converted acc. to IEC)                     |
| Conductor cross-section flexible  | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup>            |
| Conductor cross-section, flexible [AWG]   | 26 ... 10 (converted acc. to IEC)                     |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>            |
| 2 conductors with same cross section, rigid   | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>          |
| 2 conductors with same cross section, flexible  | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>          |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve       | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>          |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup>             |
| Nominal cross section   | 4 mm <sup>2</sup>                                     |
| Nominal current   | 32 A  |
| Maximum load current  | 32 A (with 6 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage   | 800 V   |

# UPBV 4/ 1 GNYE - Plug



3045279

<https://www.phoenixcontact.com/us/products/3045279>

## Dimensions

|        |         |
|--------|---------|
| Width  | 6.2 mm  |
| Height | 22 mm   |
| Depth  | 48.5 mm |
| Length | 22 mm   |
| Pitch  | 6.2 mm  |

## Material specifications

|   |              |
|---|--------------|
| Color   | green-yellow |
| Flammability rating according to UL 94                                  | V0           |
| Insulating material group   | I            |
| Insulating material   | PA           |
| Static insulating material application in cold                          | -60 °C       |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C       |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C       |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3  |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3  |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3  |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3  |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg     |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed       |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed       |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed       |

## Environmental and real-life conditions

### Ambient conditions

|  |   |
|--|---|
| Ambient temperature (operation)          | -60 °C (max. operating temperature see derating curve)                    |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C   |
| Permissible humidity (operation)         | 20 % ... 90 %   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

## Standards and regulations

|                                  |           |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|

## Drawings

Diagram



The figure shows the derating curve of the UT 4/1P... terminal block in connection with the UPVB 4 plug

# UPBV 4/ 1 GNYE - Plug

3045279

<https://www.phoenixcontact.com/us/products/3045279>



Circuit diagram



# UPBV 4/ 1 GNYE - Plug



3045279

<https://www.phoenixcontact.com/us/products/3045279>


## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3045279>

 **CSA**  
Approval ID: 13631

 **cULus Recognized**  
Approval ID: E60425

|                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|----------------------------|-----------------------|-----------------------|-------------------|----------------------|
| <b>B</b>                   |                       |                       |                   |                      |
|                            | 600 V                 | 30 A                  | 26 - 10           | -                    |
| Multi-conductor connection | 600 V                 | 30 A                  | 26 - 14           | -                    |
| <b>C</b>                   |                       |                       |                   |                      |
|                            | 600 V                 | 30 A                  | 26 - 10           | -                    |
| Multi-conductor connection | 600 V                 | 30 A                  | 26 - 14           | -                    |

 **CSA**  
Approval ID: 13631

 **EAC**  
Approval ID: KZ7500651131219505

# UPBV 4/ 1 GNYE - Plug

3045279

<https://www.phoenixcontact.com/us/products/3045279>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250306 |
| ECLASS-15.0 | 27250306 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002021 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UPBV 4/ 1 GNYE - Plug



3045279

<https://www.phoenixcontact.com/us/products/3045279>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 4260113b-70a8-48e4-ac4e-a615a590064a |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.031 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)