

CGS-AH 50 SET - Cover

3071410

<https://www.phoenixcontact.com/us/products/3071410>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover, packed in pairs, depth: 54.5 mm, width: 63 mm, height: 214 mm, color: gray



Your advantages

- Route preassembled cables and wires easily, thanks to the patent-pending swivel joint
- Subsequent wiring is easy, thanks to swivel joint openings that can be operated without tools
- Integrated flanges with strain relief make assembly quick and easy
- Easily plan cable harnesses: the cable length is predefined through the swivel arm
- Mechanical cable protection and bundling, thanks to protective covers that can be attached without tools

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3071410 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BE06 |
| Product key | BE61ZX |
| GTIN | 4055626289168 |
| Weight per piece (including packing) | 222 g |
| Weight per piece (excluding packing) | 215.5 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

CGS-AH 50 SET - Cover

3071410

<https://www.phoenixcontact.com/us/products/3071410>



Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Cover profile |
|--------------|---------------|

Dimensions

| | |
|--------|---------|
| Width | 63 mm |
| Height | 214 mm |
| Depth | 54.5 mm |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Material | PC |
| Flammability rating according to UL 94 | V0 |
| Components | halogen-free |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C ... 85 °C |
| Ambient temperature (storage/transport) | -25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

CGS-AH 50 SET - Cover

3071410

<https://www.phoenixcontact.com/us/products/3071410>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27182811 |
| ECLASS-15.0 | 27182811 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002620 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

CGS-AH 50 SET - Cover

3071410

<https://www.phoenixcontact.com/us/products/3071410>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.749 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com