

UK 10-DREHSI-EX (6,3X32) - Fuse modular terminal block



3073966

<https://www.phoenixcontact.com/us/products/3073966>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse modular terminal block, fuse type: Glass / ceramics / ..., fuse type: G / 6,3 x 32, nom. voltage: 400 V, nominal current: 10 A, connection method: Screw connection, Rated cross section: 1.5 mm², cross section: 0.5 mm²- 16 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, color: black

The figure shows version UK 10-DREHSI (5x20)

Your advantages

- Fuse terminal block for explosion protection

Commercial data

Item number	3073966
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE12
Product key	BE1235
GTIN	4046356343138
Weight per piece (including packing)	34.756 g
Weight per piece (excluding packing)	34.756 g
Customs tariff number	85369095
Country of origin	PL

UK 10-DREHSI-EX (6,3X32) - Fuse modular terminal block



3073966

<https://www.phoenixcontact.com/us/products/3073966>

Technical data

Notes

Order information:	Fuse-link not supplied as standard
--------------------	------------------------------------

Product properties

Product type	Fuse terminal block
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Fuse type	Glass / ceramics / ...
Rated surge voltage	4 kV
Maximum power dissipation for nominal condition	2.43 W
Fuse	G / 6,3 x 32

Connection data

Number of connections per level	2
Nominal cross section	16 mm ²

Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M4
Tightening torque	1.5 ... 1.8 Nm
Stripping length	11 mm
Internal cylindrical gage	B6
Connection in acc. with standard	IEC 60947-7-3
Conductor cross-section rigid	0.5 mm ² ... 16 mm ²
Cross section AWG	20 ... 6 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 16 mm ²
Conductor cross-section, flexible [AWG]	20 ... 6 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 10 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 10 mm ²
Cross-section with insertion bridge, rigid	10 mm ²
Cross-section with insertion bridge, flexible	10 mm ²
2 conductors with same cross section, rigid	0.5 mm ² ... 4 mm ²
2 conductors with same cross section, flexible	0.5 mm ² ... 4 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	0.5 mm ² ... 4 mm ²
2 conductors with the same cross section, flexible, with TWIN	0.5 mm ² ... 10 mm ²

UK 10-DREHSI-EX (6,3X32) - Fuse modular terminal block



3073966

<https://www.phoenixcontact.com/us/products/3073966>

ferrule with plastic sleeve	
Nominal cross section	1.5 mm ²
Nominal current	10 A
Maximum load current	10 A
Nominal voltage	400 V
	800 V (As a disconnect terminal block)

Ex data

Rated data (ATEX/IECEX)

Identification	⊕ II 3 GD Ex ec IIC Gc
Operating temperature range	-50 °C ... 125 °C
Ex-certified accessories	1205066 SZS 1,0X4,0 VDE 1201442 E/UK
Rated insulation voltage	250 V
output	(Permanent)

Ex level General

Rated voltage	275 V
Rated current	10 A
Maximum load current	10 A

Ex connection data General

Torque range	1.5 Nm ... 1.8 Nm
Nominal cross section	16 mm ²
Rated cross section AWG	6
Connection capacity rigid	0.5 mm ² ... 16 mm ²
Connection capacity AWG	20 ... 6
Connection capacity flexible	0.5 mm ² ... 16 mm ²
Connection capacity AWG	20 ... 6
2 conductors with same cross section, solid	0.5 mm ² ... 4 mm ²
2 conductors with the same cross-section AWG rigid	20 ... 10
2 conductors with same cross section, stranded	0.5 mm ² ... 4 mm ²
2 conductors with the same cross-section AWG flexible	20 ... 10

Dimensions

Width	12 mm
Height	62 mm
Depth on NS 32	62.2 mm
Depth on NS 35/7,5	57.2 mm
Depth on NS 35/15	64.7 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V2
Insulating material group	I

UK 10-DREHSI-EX (6,3X32) - Fuse modular terminal block



3073966

<https://www.phoenixcontact.com/us/products/3073966>

Insulating material	PA
---------------------	----

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-3
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 32

UK 10-DREHSI-EX (6,3X32) - Fuse modular terminal block



3073966

<https://www.phoenixcontact.com/us/products/3073966>

Drawings

Circuit diagram



UK 10-DREHSI-EX (6,3X32) - Fuse modular terminal block





3073966


<https://www.phoenixcontact.com/us/products/3073966>


Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3073966>

 ATEX Approval ID: KEMA10ATEX0096U				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	10 A	-	0.5 - 16

 IECEX Approval ID: IECEx KEM10.0054U				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	10 A	-	0.5 - 16

 CCC Approval ID: 2020322313000632				
---	--	--	--	--

 UKCA-EX Approval ID: DEKRA 22UKEX6025U				
--	--	--	--	--

 EAC Ex Approval ID: KZ 7500525010101950				
---	--	--	--	--

UK 10-DREHSI-EX (6,3X32) - Fuse modular terminal block



3073966

<https://www.phoenixcontact.com/us/products/3073966>

Classifications

ECLASS

ECLASS-13.0	27250113
ECLASS-15.0	27250113

ETIM

ETIM 10.0	EC000899
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UK 10-DREHSI-EX (6,3X32) - Fuse modular terminal block



3073966

<https://www.phoenixcontact.com/us/products/3073966>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.465 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com