


RBO 12-3L/N - Bolt connection terminal block



3076264

<https://www.phoenixcontact.com/us/products/3076264>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bolt connection terminal block, nom. voltage: 1000 V, nominal current: 415 A, number of connections: 8, number of positions: 4, connection method: Bolt connection, Rated cross section: 240 mm², 1 level, mounting type: NS 35/7,5, NS 35/15, direct screw connection, color: gray/blue

Commercial data

Item number	3076264
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BE4412
GTIN	4046356653503
Weight per piece (including packing)	1,493 g
Weight per piece (excluding packing)	1,493 g
Country of origin	CN

RBO 12-3L/N - Bolt connection terminal block



3076264

<https://www.phoenixcontact.com/us/products/3076264>

Technical data

Product properties

Product type	Bolt connection terminal block
Number of positions	4
Pitch	49 mm
Number of connections	8
Number of rows	1
Potentials	4

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
---------------------	------

Connection data

Number of connections per level	8
Nominal cross section	240 mm ²

1 level

Connection method	Bolt connection
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal cross section	240 mm ²
Nominal current	415 A
Maximum load current	415 A (with 240 mm ² conductor cross-section)
Nominal voltage	1000 V

Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	10 mm ² ... 240 mm ²
Cross section range AWG	8 ... 500 kcmil (converted acc. to IEC)
Hole diameter	13 mm
Width	38 mm
Bolt diameter	12 mm
Screw thread	M12
Tightening torque	14 ... 30 Nm

Connection in acc. with standard	DIN 46235:1983-07
Cross section	10 mm ² ... 240 mm ²
Cross section range AWG	8 ... 500 kcmil (converted acc. to IEC)
Hole diameter	13 mm
Width	42 mm

RBO 12-3L/N - Bolt connection terminal block




3076264

<https://www.phoenixcontact.com/us/products/3076264>

Bolt diameter	12 mm
Screw thread	M12
Tightening torque	14 ... 30 Nm

Dimensions

Dimensional drawing	
Width	196 mm
Pitch	49 mm

Material specifications

Color	gray/blue
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15
	direct screw connection

RBO 12-3L/N - Bolt connection terminal block




3076264

<https://www.phoenixcontact.com/us/products/3076264>

Drawings

Dimensional drawing



RBO 12-3L/N - Bolt connection terminal block



3076264

<https://www.phoenixcontact.com/us/products/3076264>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com