

# MTKD-NICR/CUNI EX - Thermoelectric voltage terminal block pair

3100076

<https://www.phoenixcontact.com/us/products/3100076>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Thermoelectric voltage terminal block pair, TC type E, nom. voltage: 400 V, nominal current: 1 A, number of connections: 4, number of positions: 2, connection method: Screw connection, 1 level, cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, NS 32, color: gray

The figure shows version  
MTKD-CU/CUNI

## Your advantages

- These special terminal blocks are used to extend thermocouple equalizing conductors in corresponding measuring circuits
- This ensures that no false thermoelectric voltages occur at the junctions of the thermocouple/terminal block/compensating line and that the basic values in accordance with EN 60584/DIN EN 60584 are observed
- The equalizing conductors are made from materials which, up to temperatures of 200°C, have the same thermal characteristics as the corresponding thermocouples

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3100076       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE12          |
| Product key                          | BE1211        |
| GTIN                                 | 4046356678155 |
| Weight per piece (including packing) | 15.48 g       |
| Weight per piece (excluding packing) | 15.48 g       |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# MTKD-NICR/CUNI EX - Thermoelectric voltage terminal block pair



3100076

<https://www.phoenixcontact.com/us/products/3100076>

## Technical data

### Product properties

|                       |                             |
|-----------------------|-----------------------------|
| Product type          | Feed-through terminal block |
| Product family        | MTK                         |
| Number of positions   | 2                           |
| Number of connections | 4                           |
| Number of rows        | 1                           |
| Potentials            | 1                           |

### Electrical properties

|   |        |
|---|--------|
| Maximum power dissipation for nominal condition | 0.77 W |
|---|--------|

### Connection data

|                                 |                     |
|---------------------------------|---------------------|
| Number of connections per level | 4                   |
| Nominal cross section           | 2.5 mm <sup>2</sup> |

#### 1 level

|   |   |
|---|---|
| Connection method   | Screw connection  |
| Screw thread  | M3  |
| Tightening torque   | 0.6 ... 0.8 Nm  |
| Stripping length  | 7 mm  |
| Internal cylindrical gage   | A3  |
| Connection in acc. with standard                                  | IEC 60947-7-1   |
| Conductor cross-section rigid                                     | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>                           |
| Cross section AWG   | 24 ... 12 (converted acc. to IEC)                                   |
| Conductor cross-section flexible                                  | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                         |
| Conductor cross-section, flexible [AWG]                           | 24 ... 14 (converted acc. to IEC)                                   |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                         |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                         |
| Nominal current   | 1 A   |
| Maximum load current  | 1 A (with 4 mm <sup>2</sup> conductor cross-section)                |
| Nominal voltage   | 400 V (Voltage to the neighboring feed-through terminal block MTK.) |

### Ex data

#### Rated data (ATEX/IECEx)

|                             |   |
|-----------------------------|---|
| Identification              | ⊕ II 2 G Ex eb IIC Gb                                       |
| Operating temperature range | -50 °C ... 110 °C   |
| Ex-certified accessories    | 3101029 D-MTK<br>3101223 ATS-MTK<br>1205066 SZS 1,0X4,0 VDE |

# MTKD-NICR/CUNI EX - Thermoelectric voltage terminal block pair



3100076

<https://www.phoenixcontact.com/us/products/3100076>

|                          |                                  |
|--------------------------|----------------------------------|
|                          | 1201442 E/UK                     |
| Ex temperature increase  | 5 K (1.1 A / 1 mm <sup>2</sup> ) |
| Rated insulation voltage | 250 V                            |
| output                   | (Permanent)                      |

## Ex level General

|                      |       |
|----------------------|-------|
| Rated voltage        | 275 V |
| Maximum load current | 1 A   |
| Contact resistance   | 11 mΩ |

## Ex connection data General

|                              |   |
|------------------------------|---|
| Torque range                 | 0.6 Nm ... 0.8 Nm                           |
| Nominal cross section        | 1 mm <sup>2</sup>                           |
| Rated cross section AWG      | 16  |
| Connection capacity rigid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Connection capacity AWG      | 24 ... 12                                   |
| Connection capacity flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Connection capacity AWG      | 24 ... 14                                   |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 10.4 mm |
| End cover width    | 1 mm    |
| Height             | 46.2 mm |
| Depth on NS 32     | 44.9 mm |
| Depth on NS 35/7,5 | 39.9 mm |
| Depth on NS 35/15  | 47.4 mm |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

# MTKD-NICR/CUNI EX - Thermoelectric voltage terminal block pair



3100076

<https://www.phoenixcontact.com/us/products/3100076>

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |
|               | NS 32     |

# MTKD-NICR/CUNI EX - Thermoelectric voltage terminal block pair



3100076

<https://www.phoenixcontact.com/us/products/3100076>

## Drawings

Circuit diagram



# MTKD-NICR/CUNI EX - Thermoelectric voltage terminal block pair





3100076


<https://www.phoenixcontact.com/us/products/3100076>


## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3100076>


|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| B  | 250 V                 | 10 A                  | 28 - 12           | -                    |
| D  | 300 V                 | 10 A                  | 28 - 12           | -                    |

|  <b>EAC Ex</b><br>Approval ID: RU C-DE.Ax07.B.03227 |  |  |  |  |
|--|--|--|--|--|
|--|--|--|--|--|

|  <b>IEC Ex</b><br>Approval ID: IECExSEV19.0061U |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  | 275 V                 | 1 A                   | -                 | 0.2 - 4              |
| Only flexible conductors   | 275 V                 | 1 A                   | -                 | 0.2 - 2.5            |

|  <b>ATEX</b><br>Approval ID: SEV19ATEX0335U |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  | 275 V                 | 1 A                   | -                 | 0.2 - 4              |
| Only flexible conductors   | 275 V                 | 1 A                   | -                 | 0.2 - 2.5            |

|  <b>UKCA-EX</b><br>Approval ID: CML 22UKEX1229U |  |  |  |  |
|--|--|--|--|--|
|--|--|--|--|--|

|  <b>EAC Ex</b><br>Approval ID: KZ 7500525010101950 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

|  <b>CCC</b><br>Approval ID: 2020322313000629 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

# MTKD-NICR/CUNI EX - Thermoelectric voltage terminal block pair



3100076

<https://www.phoenixcontact.com/us/products/3100076>

# MTKD-NICR/CUNI EX - Thermoelectric voltage terminal block pair



3100076

<https://www.phoenixcontact.com/us/products/3100076>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250115 |
| ECLASS-15.0 | 27250115 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000904 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# MTKD-NICR/CUNI EX - Thermoelectric voltage terminal block pair



3100076

<https://www.phoenixcontact.com/us/products/3100076>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.118 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)