

P-FU 6,3X32 LED 60-EX - Fuse plug

3046512

<https://www.phoenixcontact.com/us/products/3046512>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse plug, nominal current: 10 A, fuse type: G / 6,3 x 32, color: black

Your advantages

- Large-surface labeling option
- Test contacts on both sides of the fuse
- Versions with bipolar error display
- Can be used for overload/short-circuit protection

Commercial data

Item number	3046512
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1Z3X
GTIN	4046356919289
Weight per piece (including packing)	6.57 g
Weight per piece (excluding packing)	6.57 g
Customs tariff number	85369095
Country of origin	PL

P-FU 6,3X32 LED 60-EX - Fuse plug



3046512

<https://www.phoenixcontact.com/us/products/3046512>

Technical data

Notes

Notes on operation	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
--------------------	---

Product properties

Product type	Fuse
Potentials	1

Insulation characteristics

Degree of pollution	3
---------------------	---

Electrical properties

Fuse	G / 6,3 x 32
LED voltage range	30 V AC/DC ... 60 V AC/DC
LED current range	0.4 mA ... 0.86 mA

Input data

LED voltage range	30 V AC/DC ... 60 V AC/DC
-------------------	---------------------------

Connection data

Nominal current	10 A (the current is determined by the fuse used)
Maximum load current	10 A (the current is determined by the fuse used)

Dimensions

Width	8.2 mm
Height	27 mm
Length	40 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %


P-FU 6,3X32 LED 60-EX - Fuse plug

3046512

<https://www.phoenixcontact.com/us/products/3046512>

Drawings

Application drawing




Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks

P-FU 6,3X32 LED 60-EX - Fuse plug

3046512

<https://www.phoenixcontact.com/us/products/3046512>

Application drawing



Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks


P-FU 6,3X32 LED 60-EX - Fuse plug

3046512

<https://www.phoenixcontact.com/us/products/3046512>



Circuit diagram



P-FU 6,3X32 LED 60-EX - Fuse plug



3046512

<https://www.phoenixcontact.com/us/products/3046512>

Classifications

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

P-FU 6,3X32 LED 60-EX - Fuse plug



3046512

<https://www.phoenixcontact.com/us/products/3046512>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com