

A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 18 mm, sleeve length: 18 mm, color: silver-colored

Your advantages

- The insulation reliability of close connections is increased and the splicing of wires is prevented
- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3202601 |
| Packing unit | 1,000 pc |
| Minimum order quantity | 1,000 pc |
| Sales key | BH34 |
| Product key | BH3412 |
| GTIN | 4017918165758 |
| Weight per piece (including packing) | 0.144 g |
| Weight per piece (excluding packing) | 0.144 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>

Technical data

Product properties


| | |
|--------------------|--|
| Product type | Cable end sleeve |
| Conductor category | stranded conductors, class 2, 5, 6 / B, C, K, M |
| Product property | UL certified |
| | Made from soft tin-plated electrolytic copper |
| | Correspond to the requirements of DIN 46228-4 and UL 486F in terms of size |
| | Long/short-term temperature: +105°C/+120°C |

Connection data

Conductor connection

| | |
|---------------------------------------|---------------------|
| Conductor cross-section flexible max. | 1.5 mm ² |
| Conductor cross-section AWG max. | 16 |
| Stripping length | 18 mm |

Dimensions

| | |
|---|--|
| Dimensional drawing |  |
| Sleeve length | 18 mm |
| Length contact range | 18 mm |
| Maximum stripping length | 18 mm |
| Ferrule diameter | 1.7 mm |
| Sleeve wall thickness | 0.15 mm |
| Inner dimensions of the insulating collar | 2.8 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | silver-colored |
| Material | CU-DHP |
| Flammability rating according to UL 94 | HB |
| Coating | galvanically tin-plated |
| Surface characteristics | Tin-plated |
| Components | free from silicone and halogen |

Mechanical properties

Technical data

| | |
|---------------|-------|
| Sleeve length | 18 mm |
|---------------|-------|

Environmental and real-life conditions

A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>



Ambient conditions

| | |
|------------------------|--------|
| Permanent temperature | 105 °C |
| Short-term temperature | 120 °C |

Standards and regulations

| | |
|------------------------------|------------------------|
| Design according to standard | DIN 46228-1, UL 486F-A |
|------------------------------|------------------------|

A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>



Drawings

Dimensional drawing



Sleeve length (b), insulating collar inner dimension (d), sleeve diameter (k), sleeve wall thickness (j)

A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3202601>



cULus Listed

Approval ID: E488001

A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400201 |
| ECLASS-15.0 | 27400201 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000005 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27121700 |
|-------------|----------|

A 1,5 -18 - Ferrule



3202601

<https://www.phoenixcontact.com/us/products/3202601>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.002 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com