USED 27 N - Fuse modular terminal block

3048373

https://www.phoenixcontact.com/us/products/3048373

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse modular terminal block, fuse type: Screw cartridge, fuse type: D II / E 27, nom. voltage: 500 V, nominal current: 25 A, connection method: Screw connection, Rated cross section: 35 mm^2, cross section: 1.5 mm^2- 35 mm^2, mounting type: NS 35/7,5, NS 35/15, color: light gray

Your advantages

- Original DIAZED®-E 27 threads are used in closed housing
- The major advantage of the DIAZED® system is its dielectric strength of up to 500 V
- Conductor cross-sections of up to 35 mm² can be connected with the user-friendly spring-cage connection
- This fuse terminal block accommodates DIAZED® fuses

Commercial data

Item number	3048373
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BE12
Product key	BE1235
GTIN	4017918976286
Weight per piece (including packing)	143 g
Weight per piece (excluding packing)	139.05 g
Customs tariff number	85363030
Country of origin	DE

Technical data

Notes

Order information:	Fuse-link not supplied as standard
Note on application	for NEOZED fuse-links

Product properties

Product type	Fuse terminal block
Pitch	40 mm
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Fuse type	Screw cartridge
Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	4.06 W
Fuse	D II / E 27

Connection data

Number of connections per level	2
Nominal cross section	35 mm²

Level 1

Connection method	Screw connection
Screw thread	M6
Tightening torque	3.5 ... 4 Nm
Stripping length	19 mm
Internal cylindrical gage	B8
Conductor cross-section rigid	1.5 mm² ... 35 mm²
Cross section AWG	14 ... 2 (converted acc. to IEC)
Conductor cross-section flexible	1.5 mm² ... 35 mm²
Conductor cross-section, flexible [AWG]	14 ... 2 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	1.5 mm² ... 25 mm²
Flexible conductor cross-section (ferrule with plastic sleeve)	1.5 mm² ... 25 mm²
Cross-section with insertion bridge, rigid	25 mm²
Cross-section with insertion bridge, flexible	25 mm²
2 conductors with same cross section, rigid	1.5 mm² ... 10 mm²
2 conductors with same cross section, flexible	1.5 mm² ... 10 mm²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	1.5 mm² ... 10 mm²

2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm² ... 10 mm²
Nominal cross section	35 mm²
Nominal current	25 A (the current is determined by the fuse used)
Maximum load current	25 A (with 35 mm² conductor cross-section)
Nominal voltage	500 V (the voltage is determined by the fuse used)

Dimensions

Width	40 mm
Height	80 mm
Depth on NS 35/7,5	62.5 mm
Depth on NS 35/15	70 mm
Pitch	40 mm

Material specifications

Color	beige (RAL 7032)
Flammability rating according to UL 94	V2
Insulating material group	IIIb
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Mechanical properties

Mechanical data

Open side panel	No

Environmental and real-life conditions

Ambient conditions


Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 35/7,5
	NS 35/15

Drawings

Circuit diagram



Classifications

ECLASS

ECLASS-13.0	27250113
ECLASS-15.0	27250113

ETIM

ETIM 10.0	EC000899

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.78 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com