

UK 10,3-HESI N - Fuse holder

3048386

<https://www.phoenixcontact.com/us/products/3048386>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse holder, fuse type: Ceramic, fuse type: 10.3 x 38 mm, nom. voltage: 690 V AC, nominal current: 32 A, number of positions: 1, connection method: Screw connection, Rated cross section: 16 mm², cross section: 1 mm²- 16 mm², mounting type: NS 35/7,5, NS 35/15, color: black

Your advantages

- Fuse holder for fuses up to 690 V AC
- For 10 x 38 fuse-links in accordance with IEC 60269-2
- Easy to bridge

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3048386 |
| Packing unit | 12 pc |
| Minimum order quantity | 12 pc |
| Sales key | BE12 |
| Product key | BE1234 |
| GTIN | 4017918976293 |
| Weight per piece (including packing) | 45.88 g |
| Weight per piece (excluding packing) | 45.88 g |
| Customs tariff number | 85369095 |
| Country of origin | TN |

Technical data

Notes

| | |
|--------------------|------------------------------------|
| Order information: | Fuse-link not supplied as standard |
|--------------------|------------------------------------|

Product properties

| | |
|-----------------------|---------------------|
| Product type | Fuse terminal block |
| Number of positions | 1 |
| Number of connections | 2 |
| Number of rows | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------------|
| Fuse type | Ceramic |
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 3 W |
| Fuse | 10.3 x 38 mm |

Connection data

| | |
|---|---|
| Number of connections per level | 2 |
| Nominal cross section | 16 mm ² |
| Connection method | Screw connection |
| Screw thread | M5 |
| Tightening torque | 2 Nm |
| Stripping length | 15 mm |
| Internal cylindrical gage | B6 A7 |
| Connection in acc. with standard | IEC 60947-1 / -3 |
| Conductor cross-section rigid | 1 mm ² ... 16 mm ² |
| Cross section AWG | 18 ... 6 (converted acc. to IEC) |
| Conductor cross-section flexible | 1 mm ² ... 16 mm ² |
| Conductor cross-section, flexible [AWG] | 18 ... 6 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 1.5 mm ² ... 10 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 1.5 mm ² ... 10 mm ² |
| 2 conductors with same cross section, rigid | 1 mm ² ... 6 mm ² |
| 2 conductors with same cross section, flexible | 1 mm ² ... 6 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 1.5 mm ² ... 4 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 1.5 mm ² ... 4 mm ² |
| Nominal cross section | 16 mm ² |
| Nominal current | 32 A (the current and voltage are determined by the fuse) |


UK 10,3-HESI N - Fuse holder

3048386

<https://www.phoenixcontact.com/us/products/3048386>

| | |
|----------------------|---|
| Maximum load current | 32 A (the current and voltage are determined by the fuse) |
| Nominal voltage | 690 V AC (the current and voltage are determined by the fuse) |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 17.6 mm |
| Height | 79.3 mm |
| Depth on NS 35/7,5 | 64 mm |
| Depth on NS 35/15 | 71.5 mm |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| Flammability rating according to UL 94 | V2 |
| Insulating material group | III |
| Insulating material | PA |
| Relative insulation material temperature index (Elec., UL 746 B) | 125 °C |

Mechanical properties

| | |
|-----------------|----|
| Mechanical data | |
| Open side panel | No |

Environmental and real-life conditions

| | |
|--|---|
| Ambient conditions | |
| Ambient temperature (operation) | -50 °C ... 85 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|------------------|
| Connection in acc. with standard | IEC 60947-1 / -3 |
|----------------------------------|------------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

UK 10,3-HESI N - Fuse holder


3048386

<https://www.phoenixcontact.com/us/products/3048386>




Drawings

Dimensional drawing



Schematic diagram




UK 10,3-HESI N - Fuse holder

3048386

<https://www.phoenixcontact.com/us/products/3048386>



Circuit diagram



UK 10,3-HESI N - Fuse holder



3048386

<https://www.phoenixcontact.com/us/products/3048386>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3048386>



UL Recognized

Approval ID: E244294



CSA

Approval ID: 274201

UK 10,3-HESI N - Fuse holder



3048386

<https://www.phoenixcontact.com/us/products/3048386>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250113 |
| ECLASS-15.0 | 27250113 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000899 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UK 10,3-HESI N - Fuse holder



3048386

<https://www.phoenixcontact.com/us/products/3048386>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.309 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com