MPS-MT/ 4MM - Test plug

3048577

https://www.phoenixcontact.com/us/products/3048577

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, with solder connection up to 1 mm^2 conductor cross-section, number of positions: 1, color: silver-colored

Your advantages

- The test plug makes contact in all test sockets with a 4 mm diameter
- Two-piece test plug for individual plug color combinations

Commercial data

Item number	3048577
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4046356072779
Weight per piece (including packing)	2.03 g
Weight per piece (excluding packing)	1.94 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Test plug terminal block
Number of positions	1

Electrical properties

Nominal voltage U_N	60 V DC (30 V AC)
Nominal current I_N	16 A

Connection data

Connection method	Solder connection

Dimensions

Height	26 mm
Length contact range	8.4 mm
Pin diameter	4.4 mm
Note on dimensions	Length without insulating sleeve

Material specifications

Color	silver-colored

Classifications

ECLASS

ECLASS-15.0	27250304
ECLASS-13.0	27250304

ETIM

ETIM 10.0	EC002555

UNSPSC

UNSPSC 21.0	20122000

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com