

HV M5/1 - High-current connector

3049107

<https://www.phoenixcontact.com/us/products/3049107>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current connector, nom. voltage: 1000 V, nominal current: 76 A, number of connections: 1, connection method: Bolt connection, Rated cross section: 16 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- Comprehensive, supplementary accessories
- For connecting up to four conductors

Commercial data

Item number	3049107
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE42
Product key	BE4211
GTIN	4046356184014
Weight per piece (including packing)	26 g
Weight per piece (excluding packing)	18.276 g
Customs tariff number	85369010
Country of origin	CN

HV M5/1 - High-current connector



3049107

<https://www.phoenixcontact.com/us/products/3049107>

Technical data

Product properties

Product type	Bolt connection terminal block
Product family	HV
Pitch	13 mm
Number of connections	1
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	2.43 W

Connection data

Number of connections per level	1
Nominal cross section	16 mm ²
Connection method	Bolt connection
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal cross section	16 mm ²
Nominal current	76 A
Maximum load current	76 A (with 16 mm ² conductor cross-section)
Nominal voltage	1000 V

Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	0.5 mm ² ... 16 mm ²
Cross section range AWG	20 ... 6 (converted acc. to IEC)
Hole diameter	5.3 mm
Width	11 mm
Bolt length	22.5 mm
Bolt diameter	5 mm
Screw thread	M5
Tightening torque	2 ... 4 Nm
Connection in acc. with standard	DIN 46235:1983-07
Cross section	6 mm ² ... 10 mm ²
Cross section range AWG	10 ... 8 (converted acc. to IEC)
Hole diameter	5.3 mm
Width	9 mm

HV M5/1 - High-current connector



3049107

<https://www.phoenixcontact.com/us/products/3049107>

Bolt length	22.5 mm
Bolt diameter	5 mm
Screw thread	M5
Tightening torque	2 ... 4 Nm
Connection in acc. with standard	DIN 46237:1970-07
Cross section	1 mm ² ... 6 mm ²
Cross section range AWG	20 ... 10 (converted acc. to IEC)
Hole diameter	5.3 mm
Width	10 mm
Bolt length	22.5 mm
Bolt diameter	5 mm
Screw thread	M5
Tightening torque	2 ... 4 Nm

Dimensions

Width	13 mm
End cover width	2 mm
Height	64 mm
Depth	56.1 mm
Depth on NS 35/7,5	56.8 mm
Depth on NS 35/15	64.3 mm
Bolt length	22.5 mm
Pitch	13 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Result	Test passed
--------	-------------

Temperature-rise test

HV M5/1 - High-current connector



3049107

<https://www.phoenixcontact.com/us/products/3049107>

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 16 mm ²	1.92 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2.2 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	5 N
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2018-05
Spectrum	Long life test category 2, bogie-mounted
Frequency	$f_1 = 5$ Hz to $f_2 = 250$ Hz
ASD level	6.12 (m/s ²) ² /Hz
Acceleration	3.12g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis

Shocks

Specification	DIN EN 50155 (VDE 0115-200):2018-05
Pulse shape	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Ambient conditions

HV M5/1 - High-current connector



3049107

<https://www.phoenixcontact.com/us/products/3049107>

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15

HV M5/1 - High-current connector





3049107


<https://www.phoenixcontact.com/us/products/3049107>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3049107>

 CSA Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
C	1000 V	76 A	-	-

 cUL Recognized Approval ID: FILE E 60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
C	1000 V	76 A	-	-

 EAC Approval ID: RU C-DE.BL08.B.00540				
---	--	--	--	--

HV M5/1 - High-current connector



3049107

<https://www.phoenixcontact.com/us/products/3049107>

Classifications

ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HV M5/1 - High-current connector



3049107

<https://www.phoenixcontact.com/us/products/3049107>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.423 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com