


# HV M8/1 - High-current connector



3049301

<https://www.phoenixcontact.com/us/products/3049301>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current connector, nom. voltage: 1000 V, nominal current: 150 A, number of connections: 1, connection method: Bolt connection, Rated cross section: 50 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: gray

## Your advantages

- Comprehensive, supplementary accessories
- For connecting up to four conductors

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3049301       |
| Packing unit                         | 25 pc         |
| Minimum order quantity               | 25 pc         |
| Sales key                            | BE42          |
| Product key                          | BE4211        |
| GTIN                                 | 4046356184052 |
| Weight per piece (including packing) | 56.58 g       |
| Weight per piece (excluding packing) | 50.084 g      |
| Customs tariff number                | 85369010      |
| Country of origin                    | CN            |

# HV M8/1 - High-current connector



3049301

<https://www.phoenixcontact.com/us/products/3049301>

## Technical data

### Product properties

|                       |                                |
|-----------------------|--------------------------------|
| Product type          | Bolt connection terminal block |
| Product family        | HV                             |
| Pitch                 | 23 mm                          |
| Number of connections | 1                              |
| Number of rows        | 1                              |
| Potentials            | 1                              |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 4.73 W |

### Connection data

|                                  |   |
|----------------------------------|---|
| Number of connections per level  | 1   |
| Nominal cross section            | 50 mm <sup>2</sup>  |
| Connection method                | Bolt connection   |
| Stripping length                 | The stripping length depends on the specification provided by the cable lug manufacturer. |
| Connection in acc. with standard | IEC 60947-7-1   |
| Nominal cross section            | 50 mm <sup>2</sup>  |
| Nominal current                  | 150 A   |
| Maximum load current             | 150 A (with 50 mm <sup>2</sup> conductor cross-section)                                   |
| Nominal voltage                  | 1000 V  |

### Cable lug connection DIN 46234:1980-03

|                                  |  |
|----------------------------------|--|
| Connection in acc. with standard | DIN 46234:1980-03                          |
| Cross section                    | 2.5 mm <sup>2</sup> ... 50 mm <sup>2</sup> |
| Cross section range AWG          | 12 ... 2 (converted acc. to IEC)           |
| Hole diameter                    | 8.4 mm                                     |
| Width                            | 18 mm                                      |
| Bolt diameter                    | 8 mm                                       |
| Screw thread                     | M8   |
| Tightening torque                | 6 ... 12 Nm                                |
| Connection in acc. with standard | DIN 46235:1983-07                          |
| Cross section                    | 16 mm <sup>2</sup> ... 35 mm <sup>2</sup>  |
| Cross section range AWG          | 6 ... 2 (converted acc. to IEC)            |
| Hole diameter                    | 8.4 mm                                     |
| Width                            | 20 mm                                      |
| Bolt diameter                    | 8 mm                                       |

# HV M8/1 - High-current connector



3049301

<https://www.phoenixcontact.com/us/products/3049301>

|                                  |   |
|----------------------------------|---|
| Screw thread                     | M8  |
| Tightening torque                | 6 ... 12 Nm                               |
| Connection in acc. with standard | DIN 46237:1970-07                         |
| Cross section                    | 2.5 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
| Cross section range AWG          | 12 ... 8 (converted acc. to IEC)          |
| Hole diameter                    | 8.4 mm                                    |
| Width                            | 14 mm                                     |
| Bolt diameter                    | 8 mm                                      |
| Screw thread                     | M8  |
| Tightening torque                | 6 ... 12 Nm                               |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 21 mm   |
| End cover width    | 2 mm    |
| Height             | 64 mm   |
| Depth              | 63.5 mm |
| Depth on NS 35/7,5 | 65.8 mm |
| Depth on NS 35/15  | 73.3 mm |
| Bolt length        | 31.5 mm |
| Pitch              | 23 mm   |

## Material specifications

|  |                 |
|--|-----------------|
| Color  | gray (RAL 7042) |
| Flammability rating according to UL 94                           | V0              |
| Insulating material group  | I               |
| Insulating material  | PA              |
| Static insulating material application in cold                   | -60 °C          |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26           | HL 1 - HL 3     |
| Surface flammability NFPA 130 (ASTM E 162)                       | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)          | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                           | passed          |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 9.8 kV      |
| Result                | Test passed |

### Temperature-rise test

|                                   |                                |
|-----------------------------------|--------------------------------|
| Requirement temperature-rise test | Increase in temperature ≤ 45 K |
| Result                            | Test passed                    |

# HV M8/1 - High-current connector



3049301

<https://www.phoenixcontact.com/us/products/3049301>

|   |             |
|---|-------------|
| Short-time withstand current 50 mm <sup>2</sup> | 6 kA        |
| Result  | Test passed |

## Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 2.2 kV      |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

|                         |             |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35       |
| Test force setpoint     | 10 N        |
| Result                  | Test passed |

## Environmental and real-life conditions

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |  |
|------------------------|--|
| Specification          | DIN EN 50155 (VDE 0115-200):2018-05              |
| Spectrum               | Long life test category 1, class B, body mounted |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$   |
| ASD level              | 0.964 (m/s <sup>2</sup> )/Hz                     |
| Acceleration           | 5.72g  |
| Test duration per axis | 5 h  |
| Test directions        | X-, Y- and Z-axis                                |
| Result                 | Test passed                                      |

### Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 5g                                |
| Shock duration                 | 30 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |
| Result                         | Test passed                       |

### Ambient conditions

|                                 |  |
|---------------------------------|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; |
|---------------------------------|--|

# HV M8/1 - High-current connector



3049301

<https://www.phoenixcontact.com/us/products/3049301>

|  |   |
|--|---|
|  | for max. short-term operating temperature, see RTI Elec.)                 |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C   |
| Permissible humidity (operation)         | 20 % ... 90 %   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# HV M8/1 - High-current connector





3049301


<https://www.phoenixcontact.com/us/products/3049301>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3049301>

|  <b>CSA</b><br>Approval ID: 13631 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| C  | 1000 V                | 150 A                 | -                 | -                           |

|  <b>cUL Recognized</b><br>Approval ID: FILE E 60425 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| C  | 1000 V                | 150 A                 | -                 | -                           |

|  <b>EAC</b><br>Approval ID: RU C-DE.BL08.B.00540 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

# HV M8/1 - High-current connector



3049301

<https://www.phoenixcontact.com/us/products/3049301>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# HV M8/1 - High-current connector



3049301

<https://www.phoenixcontact.com/us/products/3049301>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.735 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)