


# RTO 5 - Bolt connection terminal block



3049521

<https://www.phoenixcontact.com/us/products/3049521>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bolt connection terminal block, nom. voltage: 1000 V, nominal current: 41 A, number of connections: 2, connection method: Bolt connection, Rated cross section: 6 mm<sup>2</sup>, 1 level, mounting type: NS 35/7,5, NS 35/15, color: gray

## Your advantages

- Four bridge shafts per terminal block
- Terminal point always freely accessible

## Commercial data

Item number	3049521
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE43
Product key	BE4312
GTIN	4046356140829
Weight per piece (including packing)	30.773 g
Weight per piece (excluding packing)	28.57 g
Customs tariff number	85369010
Country of origin	CN

# RTO 5 - Bolt connection terminal block



3049521

<https://www.phoenixcontact.com/us/products/3049521>

## Technical data

### Product properties

Product type	Bolt connection terminal block
Product family	RTO
Number of connections	2
Number of rows	1
Potentials	1

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.31 W

### Connection data

Number of connections per level	2
Nominal cross section	6 mm <sup>2</sup>

#### 1 level

Connection method	Bolt connection
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal cross section	6 mm <sup>2</sup>
Nominal current	41 A
Maximum load current	41 A (with 6 mm <sup>2</sup> conductor cross-section)
Nominal voltage	1000 V

#### Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Cross section range AWG	20 ... 10 (converted acc. to IEC)
Hole diameter	5.3 mm
Width	10 mm
Bolt diameter	5 mm
Screw thread	M5
Tightening torque	2.5 ... 3 Nm

Connection in acc. with standard	DIN 46237:1970-07
Cross section	1 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Cross section range AWG	16 ... 10 (converted acc. to IEC)
Hole diameter	5.3 mm
Width	10 mm

# RTO 5 - Bolt connection terminal block



3049521

<https://www.phoenixcontact.com/us/products/3049521>

Bolt diameter	5 mm
Screw thread	M5
Tightening torque	2.5 ... 3 Nm
Identification color of ring cable lugs : red	1 mm <sup>2</sup>
Identification color of ring cable lugs : blue	2.5 mm <sup>2</sup>
Identification color of ring cable lugs : yellow	6 mm <sup>2</sup>

## Ex data

### Rated data (ATEX/IECEX)

Identification	⊕ II 2 G Ex eb IIC Gb
Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	3049097 D-RT 3/5
	0706647 TPNS-UK
	3049819 BE-RT 3/5
	1209868 SHN 8
	3022276 CLIPFIX 35-5
List of bridges	Plug-in bridge / FBS 2-8 / 3030284
	Plug-in bridge / FBS 3-8 / 3030297
	Plug-in bridge / FBS 4-8 / 3030307
	Plug-in bridge / FBS 5-8 / 3030310
	Plug-in bridge / FBS 6-8 / 3032470
	Plug-in bridge / FBS 10-8 / 3030323
Bridge data	39 A (6 mm <sup>2</sup> )
Ex temperature increase	40 K (39 A/6 mm <sup>2</sup> )
for bridging with bridge	550 V
- At bridging between non-adjacent terminal blocks	352 V
- At cut-to-length bridging with cover	275 V
- At cut-to-length bridging with partition plate	550 V
Rated insulation voltage	500 V
output	(Permanent)

### Ex level General

Rated voltage	550 V
Rated current	39 A
Maximum load current	39 A
Contact resistance	0.41 mΩ

### Ex connection data General

Torque range	2.5 Nm ... 3 Nm
Nominal cross section	6 mm <sup>2</sup>
Rated cross section AWG	10
Connection capacity rigid	0.1 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Connection capacity AWG	26 ... 10
Connection capacity flexible	0.1 mm <sup>2</sup> ... 6 mm <sup>2</sup>

# RTO 5 - Bolt connection terminal block



3049521

<https://www.phoenixcontact.com/us/products/3049521>

Connection capacity AWG	26 ... 10
-------------------------	-----------

## Dimensions

Width	16.3 mm
End cover width	2.2 mm
Height	66 mm
Depth on NS 35/7,5	49.9 mm
Depth on NS 35/15	57.4 mm

## Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

## Electrical tests

### Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

### Temperature-rise test

Requirement temperature-rise test	Increase in temperature $\leq$ 45 K
Result	Test passed
Short-time withstand current 6 mm <sup>2</sup>	0.72 kA
Result	Test passed

### Power-frequency withstand voltage

Test voltage setpoint	2.2 kV
Result	Test passed

## Mechanical properties

### Mechanical data

Open side panel	Yes
-----------------	-----

## Mechanical tests

### Mechanical strength

Result	Test passed
--------	-------------

### Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	5 N
Result	Test passed

## Environmental and real-life conditions

### Needle-flame test

Time of exposure	30 s
Result	Test passed

### Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
ASD level	$1.857 \text{ (m/s}^2\text{)}^2\text{/Hz}$
Acceleration	0.8g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

### Shocks

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Pulse shape	Half-sine
Acceleration	5g
Shock duration	30 ms
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

## Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

## Mounting

# RTO 5 - Bolt connection terminal block



3049521

<https://www.phoenixcontact.com/us/products/3049521>

Mounting type	NS 35/7,5
	NS 35/15

# RTO 5 - Bolt connection terminal block



3049521

<https://www.phoenixcontact.com/us/products/3049521>

## Drawings

Circuit diagram



# RTO 5 - Bolt connection terminal block





3049521


<https://www.phoenixcontact.com/us/products/3049521>


## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3049521>


	<b>IECEE CB Scheme</b> Approval ID: DE1-62814
---	--

	<b>VDE approval of drawings</b> Approval ID: 40022553			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	1000 V	41 A	-	0.14 - 6

	<b>cULus Recognized</b> Approval ID: E60425			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
B				
	600 V	30 A	-	-
C				
	600 V	30 A	-	-

	<b>EAC Ex</b> Approval ID: KZ 7500525010101950
---	---

	<b>IECEX</b> Approval ID: IECEXPTB08.0063U			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	550 V	39 A	-	0.1 - 6

	<b>ATEX</b> Approval ID: PTB09ATEX1003U			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	550 V	39 A	-	0.1 - 6

	<b>CCC</b> Approval ID: 2020322313000627
---	---

# RTO 5 - Bolt connection terminal block



3049521

<https://www.phoenixcontact.com/us/products/3049521>



**UKCA-EX**

Approval ID: CSAE 22UKEX1085U

# RTO 5 - Bolt connection terminal block



3049521

<https://www.phoenixcontact.com/us/products/3049521>

## Classifications

### ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

### ETIM

ETIM 10.0	EC000897
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RTO 5 - Bolt connection terminal block



3049521

<https://www.phoenixcontact.com/us/products/3049521>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.247 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)