


RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block with bolt connection method, cross section: 2.5 - 35 mm², AWG: 14 - 2, width 20.2 mm, color: blue

Your advantages

- Four bridge shafts per terminal block
- Terminal point always freely accessible

Commercial data

Item number	3049864
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE43
Product key	BE4312
GTIN	4046356284684
Weight per piece (including packing)	80.468 g
Weight per piece (excluding packing)	80.468 g
Customs tariff number	85369010
Country of origin	CN

RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>

Technical data

Product properties

Product type	Bolt connection terminal block
Product family	RTO
Number of positions	1
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	4.06 W

Connection data

Number of connections per level	2
Nominal cross section	35 mm ²

1 level

Connection method	Bolt connection
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-1
Nominal cross section	35 mm ²
Nominal current	125 A
Maximum load current	125 A (with 35 mm ² conductor cross-section)
Nominal voltage	1000 V

Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	2.5 mm ² ... 35 mm ²
Cross section range AWG	(converted acc. to IEC)
Hole diameter	8.4 mm
Width	16 mm
Bolt diameter	8 mm
Screw thread	M8
Tightening torque	6 ... 10 Nm
Connection in acc. with standard	DIN 46235:1983-07
Cross section range AWG	(converted acc. to IEC)
Hole diameter	8.4 mm
Width	14 mm

RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>

Bolt diameter	8 mm
Screw thread	M8
Tightening torque	6 ... 10 Nm
Connection in acc. with standard	DIN 46237:1970-07
Cross section	2.5 mm ² ... 6 mm ²
Cross section range AWG	(converted acc. to IEC)
Hole diameter	8.4 mm
Width	14 mm
Bolt diameter	8 mm
Screw thread	M8
Tightening torque	6 ... 10 Nm
Identification color of ring cable lugs : blue	2.5 mm ²
Identification color of ring cable lugs : yellow	6 mm ²

Ex data

Rated data (ATEX/IECEX)

Identification	⊕ II 2 G Ex eb IIC Gb
Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	3049194 D-RT 8 3003062 TPN-UK 1209923 SHN 13 3022276 CLIPFIX 35-5
List of bridges	Plug-in bridge / FBS 2-10 / 3005947 Plug-in bridge / FBS 5-10 / 3005948
Bridge data	57 A (10 mm ²)
Ex temperature increase for bridging with bridge	40 K (123 A / 35 mm ²) 690 V
Rated insulation voltage output	630 V (Permanent)

Ex level General

Rated voltage	690 V
Rated current	123 A
Maximum load current	123 A
Contact resistance	0.09 mΩ

Ex connection data General

Torque range	6 Nm ... 10 Nm
Nominal cross section	35 mm ²
Rated cross section AWG	2
Connection capacity rigid	2.5 mm ² ... 35 mm ²
Connection capacity AWG	14 ... 2
Connection capacity flexible	2.5 mm ² ... 35 mm ²
Connection capacity AWG	14 ... 2

RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>

Dimensions

Width	20.2 mm
End cover width	2.2 mm
Height	84 mm
Depth	63.2 mm
Depth on NS 35/7,5	63.8 mm
Depth on NS 35/15	71.3 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>

Mounting

Mounting type	NS 35/7,5
	NS 35/15

RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>

Drawings

Circuit diagram



RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3049864>



IECEE CB Scheme

Approval ID: DE1-62814



VDE approval of drawings

Approval ID: 40022553

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	1000 V	125 A	-	2.5 - 35



cULus Recognized

Approval ID: E60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	600 V	130 A	-	-
C				
	600 V	130 A	-	-



EAC Ex

Approval ID: KZ 7500525010101950



IECEX

Approval ID: IECEXPTB08.0063U

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	690 V	123 A	-	2.5 - 35



ATEX

Approval ID: PTB09ATEX1003U

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	690 V	123 A	-	2.5 - 35



CCC

Approval ID: 2020322313000627

RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>



UKCA-EX

Approval ID: CSAE 22UKEX1085U

RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>

Classifications

ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RTO 8 BU - Bolt connection terminal block



3049864

<https://www.phoenixcontact.com/us/products/3049864>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com