


# RTO 3-PE-TC - Protective conductor terminal block



3049958

<https://www.phoenixcontact.com/us/products/3049958>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective conductor terminal block, Note: the BE-RT... path extension is to be used for non-insulated cable lugs (see accessories)., nom. voltage: 1000 V, nominal current: 24 A, number of connections: 2, connection method: Bolt connection, 1 level, mounting type: NS 35/7,5, NS 35/15, color: green-yellow

## Your advantages

- Low contact resistance
- Green-yellow housing
- Another labeling option
- Corrosion-free terminal points

## Commercial data

Item number	3049958
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE43
Product key	BE4312
GTIN	4046356431378
Weight per piece (including packing)	24.718 g
Weight per piece (excluding packing)	24.718 g
Customs tariff number	85369010
Country of origin	CN

# RTO 3-PE-TC - Protective conductor terminal block



3049958

<https://www.phoenixcontact.com/us/products/3049958>

## Technical data

### Product properties

Product type	Bolt connection terminal block
Product family	RTO
Number of connections	2
Number of rows	1
Potentials	1

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	0.77 W

### Connection data

Grounding foot	Yes
Number of connections per level	2
Nominal cross section	2.5 mm <sup>2</sup>

#### 1 level

Connection method	Bolt connection
Note	Please observe the current carrying capacity of the DIN rails.
Stripping length	The stripping length depends on the specification provided by the cable lug manufacturer.
Connection in acc. with standard	IEC 60947-7-2
Nominal current	24 A
Nominal voltage	1000 V

#### Cable lug connection DIN 46234:1980-03

Connection in acc. with standard	DIN 46234:1980-03
Cross section	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Cross section range AWG	20 ... 14 (converted acc. to IEC)
Hole diameter	3.2 mm
Width	6 mm
Bolt diameter	3 mm
Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm

Connection in acc. with standard	DIN 46237:1970-07
Cross section	1 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Cross section range AWG	18 ... 14 (converted acc. to IEC)
Hole diameter	3.2 mm
Width	6 mm

# RTO 3-PE-TC - Protective conductor terminal block



3049958

<https://www.phoenixcontact.com/us/products/3049958>

Bolt diameter	3 mm
Screw thread	M3
Tightening torque	0.6 ... 0.8 Nm
Identification color of ring cable lugs : red	1 mm <sup>2</sup>
Identification color of ring cable lugs : blue	2.5 mm <sup>2</sup>

## Dimensions

Width	12.3 mm
End cover width	2.2 mm
Height	66 mm
Depth on NS 35/7,5	51 mm
Depth on NS 35/15	58.5 mm

## Material specifications

Color	green-yellow
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C

## Mechanical properties

### Mechanical data

Open side panel	Yes
-----------------	-----

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

## Standards and regulations

Connection in acc. with standard	IEC 60947-7-2
----------------------------------	---------------

## Mounting

Mounting type	NS 35/7,5
	NS 35/15

# RTO 3-PE-TC - Protective conductor terminal block




3049958

<https://www.phoenixcontact.com/us/products/3049958>

## Drawings

Circuit diagram



# RTO 3-PE-TC - Protective conductor terminal block



3049958

<https://www.phoenixcontact.com/us/products/3049958>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3049958>



**EAC**

Approval ID: RU C-DE.BL08.B.00540



**EAC**

Approval ID: KZ7500651131219505

# RTO 3-PE-TC - Protective conductor terminal block



3049958

<https://www.phoenixcontact.com/us/products/3049958>

## Classifications

### ECLASS

ECLASS-13.0	27250103
ECLASS-15.0	27250103

### ETIM

ETIM 10.0	EC000901
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RTO 3-PE-TC - Protective conductor terminal block



3049958

<https://www.phoenixcontact.com/us/products/3049958>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)